

The 2403 USB serial I/O adapter provides four RS-232, RS-422, or RS-485 serial ports for USB connectivity to legacy or non-USB compliant devices. Each port is individually configurable for RS-232, RS-422, or RS-485. Simply install the included software and connect the 2403 serial interface adapter to your USB port. The device is immediately recognized by the system. Now your non-USB peripherals can have the same connection simplicity and ease of use as USB aware peripherals.

Sealevel Systems provides I/O solutions for connectivity technology. Sealevel's commitment to providing the best I/O solutions is reflected in the [Lifetime Warranty](#) that is standard on all Sealevel manufactured I/O products.



- ▶ Each port individually configurable for as RS-232, RS-422, or RS-485
- ▶ High speed UART with 128-byte Tx FIFO and 384-byte Rx FIFO
- ▶ Data rates to 921.6K bps
- ▶ Automatic RS-485 enable/disable
- ▶ Serial and USB activity LEDs
- ▶ Hot-swappable
- ▶ Powered by USB connection
- ▶ DB-9M connectors
- ▶ 72" USB cable included

TECHNICAL SPECIFICATIONS	
Number of Ports	4
Communications Chip	USB/UART
Max. Data Rate	921.6K bps
Max. Data Distance	4000 feet
USB Spec.	1.1 Compliant 2.0 Compatible
Operating Temperature	0 - +70°C
Storage Temperature	-50° - +105°C
Humidity Range	10 - 90% R.H.
Dimensions	7.1" (L) x 5.3" (W) x 1.5" (H)