



GCS22DPKIT

## 2-Port VGA and DisplayPort KVM Switch Kit

You finally have the **flexibility to mix and match your video options** with the 2-Port VGA and DisplayPort KVM Switch Kit. Streamline and enhance the efficiency of your workstations by eliminating multiple desktop setups. With the included adapters, IOGEAR's VGA and DisplayPort KVM solution simplifies the method for **sharing two computers using one VGA monitor, keyboard and mouse**.



### Features

---

- Switch between two computers with the push of a button
- Offers the flexibility to mix and match VGA & DisplayPort computer connections
- Includes 2 x DisplayPort to VGA adapters
- No external power needed
- Cost effective, Plug-N-Play solution, no software needed
- One USB keyboard, USB mouse, and VGA monitor controls two computers
- Max resolution: 2048 x 1536, DDC2B
- 4' Long molded-in cables to simplify setup
- Compatible with PC, MAC and SUN operating platforms
- Supports Windows® 7, 8.1, 10, 11, Mac OS® X 9.0+, Linux®, Unix and other USB supported systems\*
- Full Mac keyboard support
- Supports programmable mice
- All cables included
- 2 x DisplayPort to VGA Adapters convert your DisplayPort to VGA:
  - Works with computer systems using DisplayPort
  - Compliant with Displayport Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
  - Support full DisplayPort link tracking
  - Supported resolutions:
    - Full HD 1080p
    - 1920 x 1200
    - VGA, SVGA, XGA, SXGA and UXGA at 162 MHz pixel rate
  - Support interrupt request output for expansion function
  - Support Deep Sleep Mode (suspend mode)

### Requirements

**Console:**

- 1 x VGA display

### Package Contents

- 1 x 2-Port USB Cable KVM
- 2 x DisplayPort to VGA Adapters

**www.iogear.com**



- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse

- 1 x Quick Start Guide
- 1 x Warranty Card

**Computers:**

- VGA or DisplayPort port
- USB ports
- 3.5mm audio port (optional)

**Operating Systems:**

- Windows® 7, 8.1, 10, 11
- Mac OS® X 9.0+
- Linux®, Unix and other USB supported systems\*

\*Additional drivers and support may be needed



## Specifications

FUNCTION	GCS22DPKIT	DIMENSIONS	GCS22DPKIT
Computer Connections		POP Information	
Direct	2	10" Peg Hook	3
Console Connectors		Unit Dimensions	
Monitor	VGA	Height	12.5" (31.75cm)
Keyboard	USB	Depth	0.87" (2.2cm)
Mouse	USB	Length	2.5" (6.35cm)
CPU Connectors		Unit Package Dimensions	
Monitor	2 x VGA; 2 x DisplayPort (with adapters)	Width	7.4" (18.7cm)
Keyboard & Mouse	2 x USB	Height	7.6" (19.3cm)
LEDs		Depth	2.25" (5.7cm)
On Line	Green	Master Carton	
Video Resolution	up to 2048x1536 (VGA), up to 1920x1200 (with adapters)	Width	6.5" (16.5cm)
Port Selection	Remote Pushbutton	Height	7.9" (13cm)
Cable Length	2 x 4ft KVM, 1 x 6ft Remote Pushbutton	Depth	14.9" (37.9cm)
Cable Type	Bonded USB KVM	Master Carton Qty.	6
Housing		Weight	
Case	Plastic	Master Carton Wt.	7.7lb (3.5kg)
		Unit Pack Wt.	1.2lb (0.54kg)
		Unit Wt.	0.875lb (0.39kg)