



GCS1808

8-Port USB PS/2 Combo VGA KVMP Switch (TAA Compliant)

IOGEAR's GCS1808 KVMP is a combo USB and PS/2 switch allowing access and control of up to 128* computers from a single console (keyboard, mouse, and monitor). Cascade as many as 8 additional switches to bring the total number of connected computers to 64 computers that can be controlled from a single keyboard-monitor-mouse console.



Features

- 8-Port VGA KVMP with USB and PS/2 Interface
- Maximum video resolution: up to 2048 x 1536
- **Cascade up to 2 levels - control up to 128 computers from a single console
- *** Front USB Port - for system upgrades
- Security - 2 level password protection for OSD
- Auto Scan Mode to monitor connected computers
- Broadcast Mode to send commands to all connected computers
- Rack mountable in a 19" (1U) system rack
- Multi-platform OS support - Windows®, Mac, Oracle® Solaris and Linux®
- Easy to operate - computer selection via front panel LED's, intuitive OSD (on screen display) and hotkeys
- Custom ASIC provides an auto-sensing function that recognizes the position of each station on the installation
- Fully supports DDC2B
- Firmware upgradable
- TAA Compliant

*IOGEAR's Display Emulation Technology provides the DDC support for Windows® 7

**Cascade with GCS1716 for control over 128 computers

***Only systems connected with the USB KVM cables will be able to access the front USB port for system upgrades and shared peripherals

Requirements

Console:

- VGA, SVGA, or MultiSync Monitor
- A Keyboard and Mouse (USB or PS/2)

Computers:

- VGA, SVGA, or MultiSync video graphics card with an HDB-15

Package Contents

- 1 x 8-Port USB PS/2 Combo KVM
- 1 x PS/2 KVM Cable (6ft - G2L5202P)
- 1 x USB KVM Cable (6ft - G2L5202U)
- 1 x Console Cable
- 1 x Cascade Cable
- 1 x Firmware Upgrade Cable
- 1 x Grounding Wire
- 1 x Foot Pad Set (4 Pads)

www.iogear.com



port

- PS/2 mouse and keyboard ports (6-pin mini DIN)
- 1 x USB port

Operating Systems:

- Windows(R) XP, Windows Vista(R), Windows(R) 7*, Windows(R) 8, Windows(R) 8.1, Windows 10
- Mac OS 9 to 10.x
- Oracle(R) Solaris
- Linux , Unix and other USB supported systems **

**Additional drivers and support may be needed

*IOGEAR's DynaSync provides the EDID support for Windows(R) 7

- 1 x Power Adapter
- 1 x Standard Rack Mounting Kit
- 1 x Installation Guide
- 1 x Warranty Card



Specifications

FUNCTION	GCS1808	DIMENSIONS	GCS1808
Computer Connections		Unit Dimensions	
Direct	8	Height	1.75in.
Daisy Chain or Cascading	64 (via Cascade)	Depth	6.25in.
Port Selection	Hotkeys, OSD, Button	Width	17in.
Connectors		Unit Package Dimensions	
Console	1 x SPHD-18 Male (Yellow)	Height	9.625in.
Computer/KVM	8 x SPHD-15 Female (Yellow)	Width	22in.
Power	1 x DC Jack	Depth	5.5in.
USB	1 x USB 1.1 Type A Female	Master Carton	
Reset Switch	1 x Semi-Recessed Push Button	Height	10.75in.
Switches		Width	18.25in.
F/W Upgrade	1 x Slide Switch	Depth	22.75in.
Port Selection	8 x Push Button	Master Carton Qty.	3
Emulation		Weight	
Keyboard	PS/2, USB	Master Carton Wt.	30.66lb
Mouse	PS/2, USB	Unit Pack Wt.	9.4lb
Video Resolution	VGA 2048x1536, DDC2B	Unit Wt. w/accessories	7.68lb
Power		Unit Wt.	5.58lb
Voltage	DC 5.3V		
Amps	2.4A		
Scan Interval	1-255 sec		
Environment			
Operation Temperature	0~50C		
Storage Temperature	-20~60C		
Humidity	0~80% RH, Non-condensing		
Housing			
Case	Metal		
Cable Length	1 x 6ft USB KVM Cable; 1 x 6ft PS/2 KVM Cable		