

Product availability: Stock - Normally stocked in distribution facility



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	100 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 4...AWG 2/0 (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	1.5 in

Environment

Certifications	UL listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00104 - QO 35-70A 1P;70-125A 2P CB
Discount Schedule	DE2A
GTIN	00785901501305
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7099999999999996
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------