

# Product data sheet

## Characteristics

# QO2150

QO mini breaker, 150 A, 2 pole, 120/240 V, 10 kA, plug in



Product availability: Stock - Normally stocked in distribution facility



## Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	150 A
System Voltage	120 V AC 120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

## Complementary

Interrupt Rating	10 kA at: 120/240 V AC 50/60 Hz 10 kA at: 120 V AC 50/60 Hz
Number of Panel Spaces	4
Wire Size	AWG 1...300 kcmil (copper or aluminium)
Height	3.5 in
Depth	2.91 in
Width	1.5 in

## Environment

Certifications	UL listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00082 - QO BREAKERS 150-200A
Discount Schedule	DE2A
GTIN	00785901300021
Nbr. of units in pkg.	1
Package weight(Lbs)	2.6299999999999999
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------