



Part: 2455R—01000074

Comm T-Stat Listing	Open Temp (°C)	Close Temp (°C)	OOR/COR
2455R--01000074	70	55	OPEN ON RISE

P/N	2455R--01000074		
Series	2455R Series Phenolic Automatic Reset Thermostats		
Open Temp (°C)	70	Open Tol (+/-°C)	3.0
Close Temp (°C)	55	Closed Tol (+/-°C)	6.0
OOR/COR	OPEN ON RISE		
Terminal or Lead Wire	T-146		
Bracket	B-203S		
Current/Voltage	15 Amps at 120VAC		
Contacts	Silver		
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]		
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]		
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case		
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied		
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm		
Housing Material	Phenolic		
Contacts composition	Silver/nickel alloy		
Agency Approvals and Standards	UL, CSA		