



Part Number : [2159580261](#)
Product Description : MX-DaSH Standard Male Connector Assembly, 35 Circuits, Keying Option A, Natural (White)
Series Number : 215958
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

- [2159580261_sd.pdf](#)
- [2159580150-PK-000.pdf](#)
- 3D Models and Design Files
- [2159580261_stp.zip](#)

Specifications

- [2159580000-AS-000.pdf](#)
- [2159580000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215958
Description	MX-DaSH Standard Male Connector Assembly, 35 Circuits, Keying Option A, Natural (White)
Application	Power, Wire-to-Wire
Product Name	MX-DaSH
UPC	196823255632

Physical

Circuits (maximum)	35
Color - Resin	Natural (White)
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	17.000/g
Number of Rows	4
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 2.50mm
Polarized to Mating Part	Yes

Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX-DaSH Standard Female Connector Assembly, 35 Circuits, Keying Option A, Natural (White)	<u>2159580161</u>

Use with Part(s)

Description	Part Number
Use With	1.20mm AK Male Terminals, 2.80mm Male Terminals