




Part Number : [2159580318](#)

Product Description : MX-DaSH High-Speed HSD
Female Connector Assembly, 31+1 Circuits, Keying
Option W, Purple

Series Number : 215958

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[2159580318_sd.pdf](#)

[2159580150-PK-000.pdf](#)

3D Models and Design Files

[2159580318_stp.zip](#)

Specifications

[2159580000-AS-000.pdf](#)

[2159580000-PS-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215958
Description	MX-DaSH High-Speed HSD Female Connector Assembly, 31+1 Circuits, Keying Option W, Purple
Application	Power, Wire-to-Wire
Product Name	MX-DaSH
UPC	196823256721

Physical

Circuits (maximum)	32
Color - Resin	Purple
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	26.050/g
Number of Rows	4
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 2.75mm, 2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX-DaSH High-Speed HSD Male Connector Assembly, 31+1 Circuits, Keying Option W, Purple	<u>2159580418</u>

Use with Part(s)

Description	Part Number
Use With	1.20mm and 2.80mm AK Female Terminals, HSD Jack