

Technical data sheet

Article number:
711-10400

HTAPE-POWER800

Product Group	Self-amalgamating Tapes – Silicone Rubber Tape
Product Family	HelaTape Power 800
Material	Silicone (SI)
Colour	Grey (GY)
Breaking Strength	18 N/10 mm
Dielectric Strength	23.5 kV/mm
Elongation at break	400 %
Length (L)	9.1 m
Operating Temperature	-54 °C to +180 °C
Package Content packed in	reel
Pack Cont.	9.1 m
Tensile Strength	7.0 N/mm ²
Thickness (T)	0.51 mm
Width (W)	25 mm

HF ✓

RoHS ✓