

# Product Change Notification

PCN25-26 Change in Packaging Specifications for Selected DIP and Slide Products

---

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
Tel : +33 (0)3 84 72 81 12 [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice

## Document revision

| Revision | Date          | Description | Author     |
|----------|---------------|-------------|------------|
| A        | 21 Jul , 2025 | Creation    | Anson Tong |

---

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
Tel :+33 (0)3 84 72 81 12      [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice

## Summary

|                              |   |
|------------------------------|---|
| 1. Purpose                   | 4 |
| 2. Overview                  | 4 |
| 3. Impact of Change          | 4 |
| 4. Part References affected  | 4 |
| 5. Date of application       | 4 |
| 6. Conditions of application | 4 |
| 7. Support                   | 4 |
| 8. Appendix                  | 5 |

---

### C&K

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
Tel : +33 (0)3 84 72 81 12      [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice

## 1. Purpose

To upgrade the packaging specifications of select DIP and slide products to improve quality assurance during product handling (sorting and inspection) processes at distribution hub, as well as, streamlining of delivery operations in alignment with the overall Littelfuse systems integration process.

## 2 . Overview

Change of the packaging specification, please refer to appendix.

## 3. Impact of Change

There is no impact to the Fit-Form-Function (FFF) of the switches; only MDQ and/or MOQ change are taking place.

## 4. Part references affected

Please refer to the appendix

## 5. Date of application

Last time buy date: N/A

Implementation date: Immediately

**Note:** Implementation of changes started on 30/06/25. Please consider potential impact to any orders received since then. For any inquiries, please reach out to your assigned representative.

We intend to support ongoing business as much as possible during this transition. Apologies for any inconveniences.)

## 6. Conditions of application

For any question & concerns, please feel free to contact your Sales Representative

## 7. Support

For any question, please contact your C&K sales representative.

---

### C&K

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
Tel : +33 (0)3 84 72 81 12      [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice

**Appendix- affected PNs**

| <b>DIP</b>              |                 |                 |                  |                         |            |                 |                 |                  |                         |
|-------------------------|-----------------|-----------------|------------------|-------------------------|------------|-----------------|-----------------|------------------|-------------------------|
| <b>Material Numbers</b> | <b>Original</b> |                 | <b>Change to</b> |                         |            | <b>Original</b> |                 | <b>Change to</b> |                         |
|                         | <b>MOQ</b>      | <b>Pack Qty</b> | <b>MOQ</b>       | <b>MDQ (Inner Pack)</b> |            | <b>MOQ</b>      | <b>Pack Qty</b> | <b>MOQ</b>       | <b>MDQ (Inner Pack)</b> |
| BPA02B                  | 600             | 60              | 1,800            | 1,800                   | SDA04H1SBD | 700             | 700             | 1,400            | 700                     |
| BPA02SBR                | 500             | 500             | 1,000            | 500                     | SDA05H0SBR | 750             | 750             | 1,500            | 750                     |
| BPA03BS                 | 27,000          | 45              | 27,000           | 1,350                   | SDA05H1BD  | 300             | 30              | 1,200            | 1,200                   |
| BPA03SB                 | 450             | 45              | 1,350            | 1,350                   | SDA05H1BDA | 1,200           | 30              | 24,000           | 1,200                   |
| BPA03SBR                | 500             | 500             | 1,000            | 1,000                   | SDA05H1SBD | 700             | 700             | 1,400            | 700                     |
| BPA04B                  | 350             | 35              | 9,450            | 1,050                   | SDA06H0SBD | 250             | 25              | 1,500            | 1,500                   |
| BPA04BS                 | 21,000          | 35              | 21,000           | 1,050                   | SDA06H0SBD | 750             | 750             | 1,500            | 750                     |
| BPA04SBR                | 500             | 500             | 1,000            | 500                     | SDA06H0SBR | 750             | 750             | 1,500            | 750                     |
| BPA05SBR                | 500             | 500             | 1,000            | 500                     | SDA06H1SBD | 700             | 700             | 1,400            | 700                     |
| BPA06B                  | 500             | 25              | 1,500            | 750                     | SDA07H0BD  | 1,000           | 20              | 1,600            | 800                     |
| BPA06SB                 | 500             | 25              | 1,500            | 750                     | SDA07H0SBR | 750             | 750             | 1,500            | 750                     |
| BPA06SBR                | 500             | 500             | 1,000            | 500                     | SDA07H1BD  | 1,000           | 20              | 1,600            | 800                     |
| BPA07B                  | 600             | 20              | 1,200            | 600                     | SDA08H0SB  | 200             | 20              | 1,200            | 1,200                   |
| BPA07SBR                | 500             | 500             | 1,000            | 500                     | SDA08H0SBD | 750             | 750             | 1,500            | 750                     |
| BPA08B                  | 600             | 20              | 1,200            | 600                     | SDA08H0SBR | 750             | 750             | 1,500            | 750                     |
| BPA08RB                 | 600             | 20              | 1,200            | 600                     | SDA08H1BDA | 800             | 20              | 1,600            | 800                     |
| BPA08SB                 | 600             | 20              | 1,200            | 600                     | SDA08H1SBD | 700             | 700             | 1,400            | 700                     |
| BPA08SBR                | 500             | 500             | 1,000            | 500                     | SDA09H0BD  | 1,200           | 15              | 1,200            | 600                     |
| BPA09B                  | 900             | 15              | 900              | 450                     | SDA09H0SB  | 1,005           | 15              | 900              | 900                     |
| BPA09SB                 | 450             | 15              | 900              | 450                     | SDA09H0SBD | 150             | 15              | 900              | 900                     |
| BPA09SBR                | 500             | 500             | 2,500            | 500                     | SDA09H1BD  | 1,200           | 15              | 1,200            | 600                     |
| BPA10B                  | 450             | 15              | 900              | 450                     | SDA09H1SBD | 1,005           | 15              | 900              | 900                     |
| BPA10RB                 | 1,350           | 15              | 900              | 450                     | SDA10H0B   | 150             | 15              | 1,200            | 600                     |
| BPA10SB                 | 450             | 15              | 900              | 450                     | SDA10H0BD  | 150             | 15              | 1,200            | 600                     |
| BPA10SBR                | 500             | 500             | 1,000            | 500                     | SDA10H0SBD | 150             | 15              | 900              | 900                     |
| BPA12SB                 | 2,100           | 14              | 2,100            | 420                     | SDA10H0SBR | 750             | 750             | 1,500            | 750                     |
| CRD10CM0SB              | 450             | 45              | 1,530            | 1,530                   | SDA10H1BD  | 150             | 15              | 1,200            | 600                     |
| CRD10CM0SBR             | 500             | 500             | 1,000            | 500                     | SDA10H1BDA | 1,200           | 15              | 1,200            | 600                     |
| CRD10RM0SB              | 450             | 45              | 1,530            | 1,530                   | SDA10H1SBD | 700             | 700             | 1,400            | 700                     |
| CRD10RM0SBR             | 500             | 500             | 1,000            | 500                     | SDA12H0B   | 1,120           | 14              | 1,120            | 560                     |
| CRD16CM0CB              | 450             | 45              | 1,530            | 1,530                   | SDA12H0BD  | 1,120           | 14              | 1,120            | 560                     |
| CRD16CM0SBR             | 500             | 500             | 1,000            | 500                     | SDA12H0SB  | 1,008           | 14              | 1,680            | 840                     |
| CRD16RM0AB              | 450             | 45              | 1,530            | 1,530                   | SDA12H0SBD | 1,008           | 14              | 1,680            | 840                     |
| CRD16RM0SB              | 450             | 45              | 1,530            | 1,530                   | SDA12H0SBR | 750             | 750             | 1,500            | 750                     |
| CRD16RM0SBR             | 500             | 500             | 1,000            | 500                     | SDA12H1BD  | 1,120           | 14              | 1,120            | 560                     |

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
 Tel : +33 (0)3 84 72 81 12      www.ckswitches.com

Document subject to change without prior notice

|            |        |     |               |              |  |              |       |       |              |              |
|------------|--------|-----|---------------|--------------|--|--------------|-------|-------|--------------|--------------|
| SDA02H0BD  | 600    | 60  | <b>1,200</b>  | <b>1,200</b> |  | SDA12H1SBD   | 1,008 | 14    | <b>1,680</b> | <b>840</b>   |
| SDA02H0SBR | 750    | 750 | <b>1,500</b>  | <b>750</b>   |  | SPA10AB      | 150   | 15    | <b>1,050</b> | <b>1,050</b> |
| SDA02H1SBD | 700    | 700 | <b>1,400</b>  | <b>700</b>   |  | SPA10B       | 150   | 15    | <b>1,500</b> | <b>1,500</b> |
| SDA03H0B   | 450    | 45  | <b>1,800</b>  | <b>1,800</b> |  | TDA04H0JB1   | 700   | 70    | <b>1,400</b> | <b>1,400</b> |
| SDA03H0BD  | 450    | 45  | <b>1,800</b>  | <b>1,800</b> |  | TDA04H0SB1   | 700   | 70    | <b>7,000</b> | <b>1,400</b> |
| SDA03H0SBR | 750    | 750 | <b>1,500</b>  | <b>750</b>   |  | TDA06H0JB1   | 500   | 50    | <b>1,000</b> | <b>1,000</b> |
| SDA03H1SBD | 700    | 700 | <b>1,400</b>  | <b>700</b>   |  | TDA06H0SB1   | 500   | 50    | <b>1,000</b> | <b>1,000</b> |
| SDA04H0SBD | 750    | 750 | <b>1,500</b>  | <b>750</b>   |  | TDP04H1SBD1  | 700   | 70    | <b>1,050</b> | <b>1,050</b> |
| SDA04H0SBR | 750    | 750 | <b>1,500</b>  | <b>750</b>   |  | TDP06H0SBD1  | 500   | 50    | <b>1,250</b> | <b>1,250</b> |
| SDA04H1BDA | 10,500 | 35  | <b>11,200</b> | <b>1,400</b> |  | TDP06H1SBD1  | 500   | 50    | <b>1,250</b> | <b>1,250</b> |
|            |        |     |               |              |  | TDP10H0SBD1R | 1,000 | 1,000 | <b>2,000</b> | <b>1,000</b> |

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
Tel : +33 (0)3 84 72 81 12      [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice

| Slide            |          |          |           |                  |                  |          |          |           |                  |
|------------------|----------|----------|-----------|------------------|------------------|----------|----------|-----------|------------------|
| Material Numbers | Original |          | Change to |                  | Material Numbers | Original |          | Change to |                  |
|                  | MOQ      | Pack Qty | MOQ       | MDQ (Inner Pack) |                  | MOQ      | Pack Qty | MOQ       | MDQ (Inner Pack) |
| AYZ0003          | 4,000    | 4,000    | 32,000    | 16,000           | OS0009           | 1,500    | 375      | 10,500    | 1,500            |
| AYZ0009          | 3,000    | 3,000    | 12,000    | 12,000           | OS0020           | 5,400    | 300      | 5,400     | 1,800            |
| AYZ0010          | 12,000   | 3,000    | 36,000    | 12,000           | OS0038           | 5,600    | 350      | 5,600     | 2,800            |
| AYZ0102AGRLC     | 4,000    | 4,000    | 16,000    | 16,000           | OS0053           | 5,600    | 350      | 5,600     | 1,400            |
| AYZ0102AURLC     | 4,000    | 4,000    | 32,000    | 16,000           | OS0058           | 5,600    | 35       | 5,600     | 5,600            |
| AYZ0103AGRLC     | 4,000    | 4,000    | 16,000    | 16,000           | OS0063           | 4,200    | 350      | 4,200     | 2,100            |
| AYZ0202AGRLC     | 3,000    | 3,000    | 12,000    | 12,000           | OS0064           | 57,600   | 300      | 57,600    | 1,800            |
| AYZ0202AGRLCJ    | 12,000   | 3,000    | 24,000    | 12,000           | OS102011MA1QN1   | 1,800    | 300      | 1,800     | 1,800            |
| AYZ0202AURLC     | 12,000   | 3,000    | 36,000    | 12,000           | OS102011MA1QN1C  | 1,800    | 300      | 1,800     | 1,800            |
| AYZ0203AGRLC     | 3,000    | 3,000    | 12,000    | 12,000           | OS102011MA1QS1   | 1,800    | 300      | 1,800     | 1,800            |
| G01199406        | 4,500    | 1,500    | 18,000    | 4,500            | OS102011MA1QS1C  | 1,800    | 300      | 1,800     | 1,800            |
| G01231502        | 18,240   | 95       | 18,240    | 570              | OS102011MS2QN1   | 1,800    | 300      | 1,800     | 1,800            |
| G01345903        | 12,000   | 1,000    | 12,000    | 3,000            | OS102011MS2QN1C  | 1,800    | 300      | 1,800     | 1,800            |
| G01500026        | 2,800    | 350      | 2,800     | 2,800            | OS102011MS2QS1   | 1,800    | 300      | 1,800     | 1,800            |
| G01531364        | 9,000    | 1,500    | 9,000     | 4,500            | OS102011MS2QS1C  | 1,800    | 300      | 1,800     | 1,800            |
| G01531366        | 9,000    | 1,500    | 9,000     | 4,500            | OS103011MA7QP1   | 1,200    | 150      | 1,200     | 1,200            |
| JS0001           | 6,000    | 1,000    | 3,000     | 3,000            | OS103011MA7QP1C  | 1,200    | 150      | 1,200     | 1,200            |
| JS0003           | 6,000    | 1,000    | 3,000     | 3,000            | OS103011MS8QP1   | 1,800    | 300      | 1,800     | 1,800            |
| JS0014           | 10,800   | 900      | 29,700    | 2,700            | OS103011MS8QP1C  | 1,800    | 300      | 1,800     | 1,800            |
| JS0017           | 1,800    | 900      | 9,000     | 9,000            | OS103012MU1QP1   | 2,100    | 350      | 2,100     | 2,100            |
| JS0018           | 4,000    | 1,000    | 40,000    | 4,000            | OS103012MU2QP1   | 2,100    | 350      | 2,100     | 2,100            |
| JS0019           | 10,800   | 900      | 29,700    | 2,700            | OS202011MA0QN1   | 4,000    | 500      | 4,000     | 4,000            |
| JS0022           | 4,000    | 1,000    | 32,000    | 4,000            | OS202011MA0QS1   | 4,000    | 500      | 4,000     | 4,000            |
| JS0024           | 3,000    | 1,000    | 30,000    | 3,000            | OS202011MS2QN1   | 2,800    | 200      | 2,800     | 2,800            |
| JS0026           | 1,800    | 900      | 9,000     | 9,000            | OS202011MS2QN1C  | 2,800    | 200      | 2,800     | 2,800            |
| JS0027           | 2,400    | 800      | 28,800    | 2,400            | OS202011MS2QS1   | 2,800    | 200      | 2,800     | 2,800            |
| JS0030           | 3,000    | 1,000    | 30,000    | 3,000            | OS202011MS2QS1C  | 5,600    | 200      | 5,600     | 2,800            |
| JS102000SAQN     | 4,000    | 4,000    | 16,000    | 16,000           | OS202011MV4QN1   | 1,600    | 400      | 1,600     | 1,600            |
| JS102011CQN      | 4,000    | 1,000    | 8,000     | 8,000            | OS202011MV4QN1C  | 1,600    | 400      | 1,600     | 1,600            |
| JS102011JAQN     | 4,000    | 1,000    | 4,000     | 4,000            | OS202011MV4QS1   | 1,600    | 400      | 1,600     | 1,600            |
| JS102011JCBN     | 3,000    | 1,000    | 30,000    | 3,000            | OS202011MV4QS1C  | 1,600    | 400      | 1,600     | 1,600            |
| JS102011JCQN     | 3,000    | 1,000    | 3,000     | 3,000            | OS202013MT5QN1   | 2,000    | 250      | 2,000     | 2,000            |
| JS102011SABN     | 4,000    | 1,000    | 32,000    | 4,000            | OS202013MT8QN1   | 1,600    | 200      | 1,600     | 1,600            |
| JS102011SAQN     | 4,000    | 1,000    | 4,000     | 4,000            | OS203011MA2QP1   | 2,800    | 350      | 2,800     | 2,800            |
| JS102011SCQN     | 3,000    | 1,000    | 3,000     | 3,000            | OS203011MS1QP1   | 2,700    | 450      | 2,700     | 2,700            |
| JS202011AQN      | 1,800    | 900      | 9,000     | 9,000            | OS203011MV9QN1   | 1,500    | 375      | 1,500     | 1,500            |
| JS202011JAQN     | 4,000    | 1,000    | 4,000     | 4,000            | OS203011MV9QS1   | 1,500    | 375      | 1,500     | 1,500            |

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
 Tel : +33 (0)3 84 72 81 12      www.ckswitches.com

Document subject to change without prior notice

|               |       |       |               |               |                |       |       |               |               |
|---------------|-------|-------|---------------|---------------|----------------|-------|-------|---------------|---------------|
| JS202011JCQN  | 5,200 | 1,300 | <b>5,200</b>  | <b>5,200</b>  | OS203012MU5QP1 | 2,100 | 350   | <b>2,100</b>  | <b>2,100</b>  |
| JS202011SCQN  | 3,000 | 1,000 | <b>3,000</b>  | <b>3,000</b>  | OS203013MT6QN1 | 2,000 | 200   | <b>2,000</b>  | <b>2,000</b>  |
| JS203011AQN   | 1,800 | 600   | <b>6,000</b>  | <b>6,000</b>  | OS203013MT7QN1 | 2,000 | 200   | <b>2,000</b>  | <b>2,000</b>  |
| JS203011CQN   | 6,000 | 750   | <b>6,000</b>  | <b>6,000</b>  | OS203013MT8QN1 | 1,600 | 200   | <b>1,600</b>  | <b>1,600</b>  |
| JS203011JQN   | 3,000 | 1,000 | <b>3,000</b>  | <b>3,000</b>  | PCM0007        | 3,500 | 3,500 | <b>14,000</b> | <b>14,000</b> |
| JS203011JCQN  | 2,400 | 800   | <b>2,400</b>  | <b>2,400</b>  | PCM0008        | 2,300 | 2,300 | <b>9,200</b>  | <b>9,200</b>  |
| JS203011SCQN  | 2,700 | 900   | <b>2,700</b>  | <b>2,700</b>  | PCM0010        | 2,300 | 2,300 | <b>9,200</b>  | <b>9,200</b>  |
| JS207011CQNR  | 1,500 | 750   | <b>6,000</b>  | <b>6,000</b>  | PCM0011        | 2,300 | 2,300 | <b>9,200</b>  | <b>9,200</b>  |
| JS207011JCQNR | 2,400 | 800   | <b>2,400</b>  | <b>2,400</b>  | PCM12SMTBR     | 7,000 | 3,500 | <b>28,000</b> | <b>14,000</b> |
| JS207011SCQNR | 2,400 | 800   | <b>2,400</b>  | <b>2,400</b>  | PCM12SMTR      | 3,500 | 3,500 | <b>14,000</b> | <b>14,000</b> |
| JSX08001SAQNL | 4,000 | 4,000 | <b>16,000</b> | <b>16,000</b> | PCM13SMTR      | 3,500 | 3,500 | <b>14,000</b> | <b>14,000</b> |

**C&K**

2 rue Berthollet - B.P. 359 F-39105 Dole Cedex - France  
 Tel : +33 (0)3 84 72 81 12      [www.ckswitches.com](http://www.ckswitches.com)

Document subject to change without prior notice