



PART NUMBER
10160974-001

NOTE:
TERMINAL HAND CRIMPING TOOL
1. AWG RANGE : 12 – 16 AWG
2. FOR CRIMP DETAILS PLEASE REFER
APPLICATION SPEC : GS-20-0687



TOOL PART NUMBER	AWG RANGE	TERMINAL SERIES	TERMINAL PART NUMBER	CONDUCTOR CRIMP HEIGHT	CONDUCTOR CRIMP WIDTH
10160974-001	12	10158070	10158070-XX2LF	1.87-1.97	3.20-3.30
	14		10158070-XX1LF	1.50-1.60	2.50-2.60
	16			1.45-1.55	2.50-2.60

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK POWER													
ltr	ecn no	dr	date	tolerances unless otherwise specified								title											
A	-	VIPIN	2022-02-28	angles	linear	.0±0.30				HAND CRIMPING TOOL FOR MINITEK POWER 5.7 TERMINALS													
						.00±0.20																	
				0°±2°		.000±0.10																	
				dr	VIPIN M.G	2022-02-28		Amphenol FCi		dwg no						sheet 1 of 1			size				
				enr	MITHUN PAUL	2022-02-28				10160974						A3							
				chr	MITHUN PAUL	2022-02-28				type Product Customer Drawing													
				appd	SPK	2022-02-28																	
sheet index	revision sheet	A 1																					