

multicomp PRO

Technical drawing of a 3-core cable with dimensions and markings.

Dimensions:

- Overall length: 3000 ± 50
- Stranded length: 30 ± 5
- Stranded length: 20 Min
- Stranded length: 200 ± 30
- Overall diameter: 110.5

Markings:

- INDENT MARKING : GFC-3R<VDE>KEMA-KEUR<SEMKO> <DEMKO> <NEMKO> <FIMKO> <CEBEC 618 > <DVE > <+ > <+ >
- IEEMMEQU NF-USE-1291-H05VV-F 3G 1.5mm² XXXX
- YEAR

Cross-section view:

- JACKET O.D.= $8.6 \pm 0.2 \text{ mm}$
- BROWN (30/0.26) O.D.= 3.1 mm
- BLUE (30/0.26) O.D.= 3.1 mm
- GRN/YEL (30/0.26) O.D.= 3.1 mm

Dimensions : Mil

Item	Description	Quantity	U/M
1	H05VV-F 1.5mm² 3C Black	1	EA
2	PLUG:P1234 16A/250V (Ningbo Znpn Electrical Appliance)		
3	Molded Connector:LS-19 16A/250V		
4	MINI TIE	2	
5	MINI TIE	1	
6	INFLATABLE BAG		
7	LABEL		

Description	Part Number
Power Cord, Black, IEC 60309 to IEC 60320-1 C19, 3 m, 16 A/250 V	GW-151824

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO