



GPAWC145W

GearPower 145W Multiport Charger

Just arrived!

Power up your devices with the GearPower 145W Multiport Charger. This compact and powerful charger features four USB ports, including USB-C and a USB-A ports, to simultaneously charge multiple devices at high speeds. Its versatile design and advanced technology make it the ideal travel companion for your tech-filled lifestyle.



Features

- **Powerful Charging:** Delivers up to 145W of total power output
- **Multiple Ports:** Equipped with 4 USB ports (3x USB-C, 1x USB-A)
- **USB-C 140W Charging:** Supports the latest fast-charging technology
- **Versatile Charging:** Can charge multiple devices simultaneously
- **Safety Features:** Built-in protections against overcurrent, overvoltage, short circuit, and overheating
- **Compact Design:** GaN technology allows for a portable and easy to carry charger
- **Includes USB-C to C 4ft Cable:** For high-speed charging of compatible devices up to 140W

Requirements

- USB-C Laptop, Tablet, Smartphone
- USB-C to C cable (One included)
- USB-A to C cable (**Not included**)

Package Contents

- 1x GPAWC145W Charger
- 1x USB-C to C 4ft cable
- 1x Warranty Card
- 1x Quick Start Guide



Specifications

FUNCTION	GPAWC145W
Connectors	
USB	2x USB-C Up to 140W 1x USB-C Up to 45W 1x USB-A Up to 18W
Single Port Used	USB-C1/C2: 28V5A 140W Max USB-C3: 20V2.25A 45W Max USB-A4: 12V1.5A 18W Max
Two Ports Used	USB-C1/USB-C2+USB-C3 Used: • USB-C1/C2: 20V5A 100W Max • USB-C3: 20V2.25A 45W Max USB-C1/USB-C2+USB-A4 Used: • USB-C1/C2: 20V5A 100W Max • USB-A4: 12V1.5A 18W Max USB-C1+ USB-C2 Used: • USB-C1/C2: 20V3.25A 65W Max USB-C3+USB-A4 Used: • USB-C3: 9V2.77A 25W Max • USB-A4: 12V1.5A 18W Max
Three Ports Used	USB-C1+USB-C2+USB-C3 Used: • USB-C1: 20V3.25A 65W Max • USB-C2: 20V1.5A 30W Max • USB-C3: 20V2.25A 45W Max USB-C1+USB-C2+USB-A4 Used: • USB-C1: 20V3.25A 65W Max • USB-C2: 20V1.5A 30W Max • USB-A4: 12V1.5A 18W Max USB-C1/USB-C2+USB-C3+USB-A4 Used: • USB-C1/C2: 20V5A 100W Max • USB-C3: 9V2.77A 25W Max • USB-A4: 12V1.5A 18W Max
Four Ports Used	• USB-C1: 20V3.25A 65W Max • USB-C2: 20V1.5A 30W Max • USB-C3: 9V2.77A 25W Max • USB-A4: 12V1.5A 18W Max
Power	
Output Rating	Max 28V 5A

DIMENSIONS	GPAWC65W
Unit Dimensions	
Height	3.7 in (9.5 cm)
Length	2.9 in (7.5 cm)
Width	1.1 in (2.8 cm)
Inner Pack	
Height	12.9 in (33 cm)
Length	6.6 in (17 cm)
Width	5.3 in (13.5 cm)
Inner Pack Qty.	6 pcs



DIMENSIONS	GPAWC65W
Unit Package Dimensions	
Height	6.4 in (16.5 cm)
Length	1.9 in (4.9 cm)
Width	4.29 in (10.9 cm)
Master Carton	
Height	13.7 in (35 cm)
Length	14.2 in (36 cm)
Width	11.8 in (30 cm)
Master Carton Qty.	24 pcs
Weight	
Master Carton Wt.	28.6 lbs (13 kgs)
Inner Pack Wt.	6.74 lbs (3.06 kgs)
Unit Pack Wt.	1.05 lbs (0.48 kgs)
Unit Wt.	0.80 lbs (0.38 kgs)