



Panduct® HN3X3LG6 Base Wiring Duct

HN3X3LG6

Panduct® type HN hinged cover narrow slot wiring duct, 3 W x 3 H, 6' length, PVC, light gray.

Specifications

Duct Dimensions (In.)	3.25W x 3.06H
Product Type	Base Wiring Duct
Application	Hinged Cover Narrow Slot Wiring Duct provides wire management in general purpose applications where it is beneficial to retain cover during wire changes
Color	Light Gray
Cover Part Number	HC3LG6
Flammability Rating	UL94V-0
Includes	(1) Base
Standards Met	RoHS Compliant, UL Recognized, CSA Compliant, CE Compliant, BABA Compliant
Material	PVC
Mount Method	Mounting Holes
Measurement System	Imperial
Wiring Duct Style	Narrow Slot Wiring Duct
Wiring Duct Type	HN
Overall Length (ft.)	6
Overall Length (m)	1.83
Overall Width (In.)	3.25
Overall Width (mm)	82.6
Overall Height (In.)	3.06
Overall Height (mm)	77.7
Slot Width (In.)	0.2
Slot Width (mm)	5
Sub Brand	Panduct®
Part Features	Hinged Cover design with Narrow finger and slot design closely matches the spacing of high-density compnents.. Upper and lower scorelines allows easy finger and sidewall section removals.

Packaging Detail

UPC	07498302859
Std. Pkg. Qty.	6
Std. Pkg. Volume (cf)	0.2967
Std. Ctn. Qty.	60
Std. Ctn. Volume (cf)	2.9667