



Panduct® MC75X100WH2 Base/Cover

MC75X100WH2

The MC75X100WH2 Panduct Lead-Free PVC Narrow Slot Wiring Duct is 74.7 mm x 97.8 mm (2.94" x 3.85"). It features a narrow slot/finger design that closely matches the spacing of high-density components. Upper and lower scorelines allow for easy finger/sidewall section removal. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. Lead-free PVC. Cover included. Color - White. 10 Meters (5 sticks each) - Bases & Covers per package.

Specifications

Duct Dimensions (mm)	74.7W x97.8H
Product Type	Wiring Duct Base with Cover
Color	White
Cover Part Number	C75WH2 (included)
Flammability Rating	UL94 V-0
Includes	(1) Cover
Standards Met	RoHS Compliant, UL Recognized, CE Compliant, DIN 43659 Compliant, BABA Compliant
Material	PVC
Material Properties	Lead-Free
Mount Method	DIN Standard Mounting Holes
Measurement System	Metric
Wiring Duct Style	Narrow Slot Wiring Duct
Wiring Duct Type	MC
Overall Length (ft.)	6.6
Overall Length (m)	2
Overall Width (In.)	2.94
Overall Width (mm)	74.7
Overall Height (In.)	3.85
Overall Height (mm)	97.8
Slot Width (In.)	0.2
Slot Width (mm)	5
Sub Brand	Panduct®
Part Features	Metric PVC narrow finger and slot design closely matches the spacing of high-density components. Upper and lower scorelines allows easy finger and sidewall section removals. Base and Cover Packaged together.

Packaging Detail

UPC	07498375248
Std. Pkg. Qty.	2
Std. Pkg. Volume (cf)	0.4101
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	2.0505