



Panduct® NNC75DWH2 Solid Divider Wall

NNC75DWH2

Panduct® type NNC divider wall, 3.00" (75mm) nominal duct height, 2M length, halogen-free, white.

Specifications

Note	For installation of the divider, must use part number DB-C
Product Type	Solid Divider Wall
Application	Wiring Duct Accessory - Solid Divider Wall
Color	White
Compatible Duct Height (In.)	3
Compatible Duct Height (mm)	75
Flammability Rating	UL94V-0
Sub Brand	Panduct®
For Use With	NNC and NE Wiring Duct
Material	PPO
Material Properties	Halogen-Free
Standards Met	RoHS Compliant
Overall Length (ft.)	6.6
Overall Length (m)	2
Overall Width (In.)	0.75
Overall Width (mm)	19
Overall Height (In.)	2.55
Overall Height (mm)	64.7

Packaging Detail

UPC	07498342205
Std. Pkg. Qty.	2
Std. Pkg. Volume (cf)	0.0615
Std. Ctn. Qty.	40
Std. Ctn. Volume (cf)	1.2296