



Panduct® HC1.5LG6 Hinged Cover, Lt Gray, PVC, 0.44"x6"x1.89", PK6

HC1.5LG6

Hinged duct cover, 1.5 W x 6' length, PVC, light gray.

Specifications

Product Type	Hinged Duct Cover
Sub Brand	Panduct®
Application	Cover for Wiring Duct
Color	Light Gray
For Use With	Hinged Cover Wiring Duct 1.5" wide
Material	PVC
Standards Met	UL Recognised; Flammability Ratings: UL94 V-0; CSA Certified; CE Compliant; RoHS Compliant
Compatible Duct Width (In.)	1.5
Compatible Duct Width (mm)	38.1
Overall Length (ft.)	6
Overall Length (m)	1.83
Overall Width (In.)	1.89
Overall Width (mm)	48
Overall Height (In.)	0.44
Overall Height (mm)	11.2
Mount Method	Snap-On
Part Features	Dual-Sided hinged cover opens up to 100° from either sidewall of duct

Packaging Detail

UPC	07498313852
Std. Pkg. Qty.	6
Std. Pkg. Volume (cf)	0.0333
Std. Ctn. Qty.	120
Std. Ctn. Volume (cf)	0.6659