



# NLT4MXX-BAG

4 pole male cable connector, black metal housing, chuck type strain relief

This connector is fully compliant to the device standard IEC 62368-1, due to its component certification according to IEC 61984.

The speakON STXX Series was especially designed for heavy duty amplifier-loudspeaker applications like professional touring. The extremely rugged and durable STXX Series features an all metal housing.

## Features & Benefits

- ✓ IEC 61984 certified, IEC 62368-1 compliant
- ✓ Extremely robust metal housing and glass reinforced V-0 material insert designed for harsh and demanding environment
- ✓ Uses precise “Quick Lock” system
- ✓ Extra large solder contacts for up to 6 mm² (AWG 10) wires
- ✓ Weatherproof built-in gasket meets IP 54 protection class in mated condition

## Technical Information

| Product |             |
|---------|-------------|
| Title   | NLT4MXX-BAG |
| Gender  | male        |

**Electrical**

|                           |                                                                     |
|---------------------------|---------------------------------------------------------------------|
| Contact resistance        | < 2 mΩ                                                              |
| Dielectric strength       | 2.8 kVac                                                            |
| Insulation resistance     | >0.1 GΩ (after dampheat)                                            |
| Rated current per contact | 30 A rms continuous                                                 |
| Rated voltage             | 250 V ac                                                            |
| Attention                 | speakON is NOT to be used as an AC mains or power supply connector! |

**Mechanical**

|                |                      |
|----------------|----------------------|
| Cable O.D.     | 9 - 16 mm            |
| Lifetime       | > 5000 mating cycles |
| Wiresize       | 6 mm <sup>2</sup>    |
| Wiresize       | 10 AWG               |
| Termination    | Solder contacts      |
| Locking device | Quick Lock           |

**Material**

|                 |                                   |
|-----------------|-----------------------------------|
| Contact plating | Ag                                |
| Contacts        | Copper Alloy                      |
| Shell           | Zinc diecast, black chrome plated |
| Insert          | Polyamide (PA 66)                 |
| Strain relief   | Polyacetal (POM)                  |

| Environmental     |                          |
|-------------------|--------------------------|
| Temperature range | -30 °C to +80 °C         |
| Flammability      | UL 94 V-0                |
| Protection class  | IP 54 (mated condition)  |
| Solderability     | Complies with IEC68-2-20 |