

Thick Film Resistors KIT



RK73H1HT-KIT1

Technology	Thick Film	Operating Temperature	-55 to +155 °C
Size Inch / Metric	0201 / 0603	Temperature Coefficient	±200 ppm
Series	E24		
Resistor Range	10Ω to 1MΩ plus jumpers		
Tolerance	±1 %		
Maximum Power	0.05 W		
Maximum Voltage	25 V		

Kit Contents

Range	10Ω to 1MΩ plus jumpers
Number of values	122
Number of pieces per value	100
E-Series	E24

■Significant figures of Nominal resistance

E3	E6	E12	E24	E96	E192	E96	E192	E96	E192	E96	E192	E96	E192
10	10	10	10	100	100	178	178	316	316	562	562		
			11	101	101	180	180		320	569	569		
				102	102	182	182	324	324	576	576		
		12	12	104	104	184	184		328	583	583		
			13	105	105	187	187	332	332	590	590		
				106	106	189	189		336	597	597		
				107	107	191	191	340	340	604	604		
		15	15	109	109	193	193		344	612	612		
			16	110	110	196	196	348	348	619	619		
				111	111	198	198		352	626	626		
				113	113	200	200	357	357	634	634		
				114	114	203	203		361	642	642		
		18	18	115	115	205	205	365	365	649	649		
			20	117	117	208	208		370	657	657		
				118	118	210	210	374	374	665	665		
				120	120	213	213		379	673	673		
22	22	22	22	121	121	215	215	383	383	681	681		
			24	123	123	218	218		388	690	690		
				124	124	221	221	392	392	698	698		
				126	126	223	223		397	706	706		
		27	27	127	127	226	226	402	402	715	715		
			30	129	129	229	229		407	723	723		
				130	130	232	232	412	412	732	732		
				132	132	234	234		417	741	741		
		33	33	133	133	237	237	422	422	750	750		
			36	135	135	240	240		427	759	759		
				137	137	243	243	432	432	768	768		
				138	138	246	246		437	777	777		
		39	39	140	140	249	249	442	442	787	787		
			43	142	142	252	252		448	796	796		
				143	143	255	255	453	453	806	806		
				145	145	258	258		459	816	816		
47	47	47	47	147	147	261	261	464	464	825	825		
			51	149	149	264	264		470	835	835		
				150	150	267	267	475	475	845	845		
				152	152	271	271		481	856	856		
		56	56	154	154	274	274	487	487	866	866		
			62	156	156	277	277		493	876	876		
				158	158	280	280	499	499	887	887		
		68	68	160	160	284	284		505	898	898		
			75	162	162	287	287	511	511	909	909		
				164	164	291	291		517	920	920		
				165	165	294	294	523	523	931	931		
				167	167	298	298		530	942	942		
		82	82	169	169	301	301	536	536	953	953		
				172	172	305	305		542	965	965		
			91	174	174	309	309	549	549	976	976		
				176	176	312	312		556	988	988		