



## GRVV4U

### 4U 19" Deep Vertical Wall Mount Server Rack

The IOGEAR 4U 19-inch Deep Vertical Wall Mount Server Rack provides a robust and space-saving solution for mounting network and server equipment under the desk or on the wall. Constructed from heavy-duty steel, this rack offers exceptional durability and support for any EIA-310 compliant hardware.



## Features

---

- 4U rack height to mount equipment
- Heavy duty construction supports up to 125Lbs of equipment
- Includes cage nuts and screws for mounting
- Includes wood screws to mount rack to wooden surface.

## Requirements

---

### Installation

- Appropriate mounting hardware for the wall or surface type (Includes wood screws)
- Phillips head screwdriver

### Mounting to Square Cage Holes:

- Cage nuts (Included)
- Rack screws and washers (Included)

## Package Contents

---

- 1 x Wall-Mount Bracket
- 6 x Wood Screws
- 16 x Cage Nuts and Screws
- 1 x Quick-Start Guide



## Specifications

<b>FUNCTION</b>	<b>GRVV4U</b>	<b>DIMENSIONS</b>	<b>GRVV4U</b>
Rack Dimension		Unit Dimensions	
Rack Height	4U	Height	7.6" (19.3cm)
Max Supported Weight	125lbs	Length	19.8" (50.3cm)
Housing		Width	5.9" (15cm)
Case	Metal	Unit Package Dimensions	
		Height	7.1" (17.9cm)
		Width	8.3" (21cm)
		Depth	20.6" (52.5cm)
		Master Carton	
		Height	7.1" (17.9cm)
		Width	8.3" (21cm)
		Depth	20.6" (52.5cm)
		Master Carton Qty.	1
		Weight	
		Master Carton Wt.	3.8lb (1.7kg)
		Unit Pack Wt.	3.8lb (1.7kg)
		Unit Wt.	2.4lb (1kg)