





ISO 14001 Registered


### **RoHS** Compliant



# LP uPCI 1+1xRS232 + 1xLPT

## "SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"

**UC-203** 



#### Features

- 1+1 port RS232 + LPT
- PCI 3.0
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 115,200 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### Options



UC-203: LP uPCI 1+1xRS232 + 1xLPT

#### Description

Universal PCI providing two RS232 serial ports. and one printer port. Up to 115,200 data transfer rates and the 128 byte deep transmit and 128 byte receive FIFOS, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC.

Universal PCI is fully compatible with both 3.3Volt and 5Volt PCI slots.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

#### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows Server 2008 & Windows 2000
- Windows Vista 32 bit and 64 bit editions
- Windows Server 2003 32 bit & 64 bit Editions
- Windows XP 32 bit & 64 bit editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.




ORDER Description LP uPCI 1+1xRS232 + 1xLPT

Code UC-203

For Standard Profile see UC-475

#### +44(0) 151 220 2500 | sales@brainboxes.com | www.bra

www.brainboxes.com



# LP uPCI 1+1xRS232 + 1xLPT

#### UC-203: Full Specification

Port	Ports	1+1 x RS232 + LPT
Pin 1 DCD RS232 Pinout (9 pin Male)	Connector	DB9 connector (9 Pin Male)
Pin 2 RXD 1 5 Pin 3 TXD 1 1	FIFO size	128 RX FIFO + 128 TX FIFO
Pin 4 DTR Pin 5 GND	Operating Distance	EIA - RS232 Standard
Pin 6 DSR Pin 7 RTS Pin 8 CTS	Cable	1 PORT RS232 on fly lead + 1 Port LPT on fly lead
Port Settings	Baud Rate	115,200
J	Data Bits	5,6,7 or 8
115,200	Parity	
baud		Odd, Even, None, Mark or Space
	Stop Bits	
	Flow Control	RTS/CTS DSR/DTR XON/XOFF
	Tx/Rx Modes	Point to Point
Interface	OS Compatibility	Windows Server 2008 32 bit & 64 bit Editions
		Windows Vista 32 bit & 64 bit Editions
PCI		Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions
		Microsoft Windows 2000
	BUS	PCI 3.0 : Peripheral Component Interface
Approvals	Other Approvals	WEEE IEEC CB Scheme METL FCC Compliant
	Microsoft Approvals	Microsoft Certified Gold Partner
		Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit & 64 bit editions
		Windows Server 2003 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions
General	PCB Layers	4
	Power Consumption	180mA @ 5V, 30mA @ 12V
	Weight	0.062 Kg
	Size	0x0x0 mm
Box Content	Packaging	Installation CD including manual, Microsoft signed drivers & utilities
	Card	LP uPCI 1+1xRS232 + 1xLPT /
		1 PORT RS232 on fly lead + 1 Port LPT on fly lead
Product Support	Warranty	Lifetime (online registration required)
(FETTING SETTING	Support	Lifetime Web, Email and Phone Support from fully qualified, friendly
		staff who work in and alongside the Product Development Team
Additional	OEM option	Available for bulk buy OEM
	Made In	Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"
WINNER Manufacturer of the Year Made in the UK	Customisable	Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Datasheet Version: 3.57 Published on: 2009/7/14