





ISO 14001 Registered

### **RoHS** Compliant




# uPCI 3+1xRS232

UC-420/UC-431

## "SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"

/



#### Features

- 3+1 port RS232
- PCI 3.0
- 64 Byte Tx and 64 Byte Rx FIFOs
- Up to 115,200 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### Options



UC-420: uPCI 3+1xRS232

UC-431 uPCI 3xRS232



#### Description

Universal PCI providing four RS232 serial ports. Up to 115,200 data transfer rates and the 64 byte deep transmit and 64 byte receive FIFOS, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC.

Universal PCI is fully compatible with both 3.3Volt and 5Volt PCI slots.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

#### Software

ORDER Description uPCI 3+1xRS232 uPCI 3xRS232

Microsoft signed drivers (easy installation & robust operation) for:

- Windows Server 2008 32 bit & 64 bit Editions
- Windows Server 2008 & Windows 2000
- Windows Vista 32 bit and 64 bit editions
- Windows Server 2003 32 bit & 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



Code
UC-420
UC-431

+44(0) 151 220 2500 | sales@brainboxes.com

www.brainboxes.com



## uPCI 3+1xRS232

### UC-420/UC-431: Full Specification

0C 420/0C 451.101 5pcc		
Port	Ports	3+1 x RS232
Pin 1 DCD RS232 Pinout (9 pin Male)	Connector	DB9 connector (9 Pin Male)
Pin 2 RXD 1 5 Pin 3 TXD 1	FIFO size	64 RX FIFO + 64 TX FIFO
Pin 4 DTR Pin 5 GND	Operating Distance	EIA - RS232 Standard
Pin 6 DSR Pin 7 RTS	Cable	1 PORT RS232 on fly lead
Pin 8 CTS 6 9		
Port Settings	Baud Rate	115,200
115,200	Data Bits	5,6,7 or 8
$\rightarrow$ $\rightarrow$ $\rightarrow$ $\rightarrow$	Parity	Odd, Even, None, Mark or Space
baud	Stop Bits	1, 1.5 or 2
	Flow Control	RTS/CTS DSR/DTR XON/XOFF
	Tx/Rx Modes	Point to Point
Interface	OS Compatibility	Windows Server 2008 32 bit & 64 bit Editions
		Windows Vista 32 bit & 64 bit Editions
PCI		Windows Server 2003 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions
		Microsoft Windows 2000
	BUS	PCI 3.0 : Peripheral Component Interface
Approvals	Other Approvals	WEEE IEEC CB Scheme METL EMC: CE
	Microsoft Approvals	Microsoft Certified Gold Partner
		Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit &
		64 bit editions
SCHEME C US		Windows Server 2003 32 bit & 64 bit editions Windows XP 32 bit &
		64 bit editions
General	PCB Layers	4
	Power Consumption	210mA @ 5V, 60mA @ 12V
	Weight	0.088 Kg
	Size	130x20x120 mm
Box Content	Packaging	Installation CD including manual, Microsoft signed drivers & utilities
	Card	uPCI 3+1xRS232 / uPCI 3xRS232
		1 PORT RS232 on fly lead
Product Support	Warranty	Lifetime (online registration required)
	Support	Lifetime Web, Email and Phone Support from fully qualified, friendly
		staff who work in and alongside the Product Development Team
Additional	OEM option	Available for bulk buy OEM
Elektra O5	Made In	Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"
European Electronics Industry Awards	Customisable	Brainboxes operate a "Perfect Fit Custom Design" policy for volume
Manufacturer of the Year Adde in the UK	Customisable	users. More Info: sales@brainboxes.com
	I	

+44(0) 151 220 2500 | sales@brainboxes.com

Datasheet Version: 3.6 Published on: 2009/7/20

www.brainboxes.com

UC-420 UC-431