



9B 1 3 2 - 10 2 4
 (1) (2) (3) (4) (5) (6) (7)



1. SERIES NUMBER :
 9B : 2.54(.100") CENTER 4 SIDED SHROUDED HEADERS
2. TYPE OF CONTACT :
 1. STRAIGHT TYPE
 2. RIGHT ANGLE TYPE
3. HOUSING CONSTRUCTOR TYPES :
 1. NO LATCHES
 2. SHORT LATCHES
 3. LONG LATCHES
4. CONTACT TAIL TYPES :
 - 1 : 3.0 (FOR SOLDER TAIL)
 - 2 : 3.6 (FOR SOLDER TAIL)
 - 3 : 11.94 (FOR WRAPPING TAIL)
 - 4 : 15.49 (FOR WRAPPING TAIL)
 - 5 : 5.00 (FOR SOLDER TAIL)
5. NUMBER OF CONTACTS :
 34 : 34 Pin
 (10,14,16,20,26,30,34,40,50,60,64)
6. COLOR CODES :
 - 1 : BLUE
 - 2 : GRAY
 - 3 : BLACK
7. CONTACT FINISH :
 - 4 : ALL PLATED GOLD FLASH OVER 30u" NICKEL
 - 5 : ALL PLATED 15u" GOLD OVER 50u" NICKEL
 - 6 : ALL PLATED 30u" GOLD OVER 50u" NICKEL




研發部

TOLERANCE UNSPECIFIED		EDA INC.	
.000	±		
.00	±		
.0	±		
ANGLE	±	DRAWN 陳逸銘 9/11-98	
DESIGNER		NAME	
CHECKED		9B SERIES ORDER INFORMATION	
APPROVED		DRAWING NO.	RS109B-1
			SHEET 2/2
			REV. 1

工程師




4.4±0.2 [0.174±0.008]




SHORT LEVER




8.1±0.2 [0.320±0.008]



LONG LEVER



CONTACTS	A [*0.03937]				CONTACTS	A [*0.03937]			
	A	B	C	D		A	B	C	D
10	32.00	18.25	21.80	10.17	34	62.50	48.90	52.30	40.65
14	37.05	23.20	26.90	15.25	40	70.10	55.35	59.90	46.27
16	39.60	25.90	29.35	17.79	50	82.85	69.15	72.70	60.97
20	44.70	31.00	34.50	22.67	60	95.50	81.90	85.35	73.67
26	52.32	38.50	42.20	30.49	64	100.60	87.10	90.50	78.75
30	57.40	43.70	47.30	35.57					



MATERIAL		FINISH		TOLERANCE UNSPECIFIED		SCALE		UNIT		PART NO.	
X		X		±0.00		1:1		MM		R-S109B-1	
DRAWN		CHECKED		DESIGNED		APPROVED		DATE		REV.	
陳逸銘 11/09-98		W. H. K.		9B SERIES 成品圖 (1463)		R-S109B-1		17.11.10		1 / 2	
DRAWING NO		SHEET		AS		XS109B11					