


## **Screw Mount D-Clip**

## **Features and Benefits**

Screwed D-clips are available in 3 sizes and guarantee time and cost saving by simply pressing the cable into the holder. The flexible grip means that later removal or replacement of cables and pipes is possible. 3 different bore diameters for fixing the holder are available



The clip is held in place by a screw and the bundled cable or pipe is guided securely.



Material	Polyacetal (POM)	
Operating Temperature	-40 °C to +90 °C Continuous, (+110 °C for 500 h)	
Flammability	UL94 HB	

Technical Table											
Article-No.	Туре	Length (L)	Length (L2)	Width (W)	Wall (WT)	Fixing Hole Ø (FH)	Bundle Ø max.	Material	Colour		
211-70000	4D10	17.0	8.0	15.0	2.0	4.0	10.0	POM	Black (BK)		
211-70001	4D15	25.0	10.0	15.0	2.0	4.0	15.0	POM	Black (BK)		
211-70002	4D20	28.0	10.0	15.0	2.5	4.0	20.0	POM	Black (BK)		
211-70100	6D10	17.0	8.0	15.0	2.0	6.0	10.0	POM	Black (BK)		
211-70101	6D15	25.0	10.0	15.0	2.0	6.0	15.0	POM	Black (BK)		
211-70104	6D20	28.0	10.0	15.0	2.5	6.0	20.0	POM	Black (BK)		
211-70200	8D10	17.0	8.0	15.0	2.0	8.0	10.0	POM	Black (BK)		
211-70203	8D15	25.0	10.0	15.0	2.0	8.0	15.0	POM	Black (BK)		
211-70204	8D20	28.0	10.0	15.0	2.5	8.0	20.0	POM	Black (BK)		

All dimensions in mm. Subject to technical changes.

