

ESD PROTECTED ARE

ESD Monitored Workstation Kit

Kit Includes:

- 1x ESD Matting (600x900mm) with 10mm stud in each corner
- 1x ESD Caution Sign
- (150 x 300mm self adhesive)
- 1x Earth Facility Bracket with M5 Binding Post
 1x UK Earth Bonding Point 2x10mm Studs and
- built in tester
- 1x Power Supply Unit for EBP
- 1x10mm Fabric Adjustable Wrist Strap Hypo Allergenic
- 1x10mm Coiled Earth Lead
- 1x10mm Straight Lead
- 1x Instruction Leaflet

Matting Features:

- Reflection breaking surface to reduce glare and improve operator comfort
- Protection against small collisions
- Prevention of sliding of delicate components thanks to excellent friction coefficient
- · Heating resistance: does not melt or burn coming into contact with hot metal parts or soldering debris
- · Oil resistance: this product resists most oils
- Suitable for loose laying: does not require application with adhesive
- Good resistance to scratches and excellent flexibility and comfort

Matting Details		
Material	Static dissipative	
Thickness	2mm	
Surface	Reflection breaking surface	
Tester	ETS 406C Static Decay Meter, 3M Model 701 Test Kit for Static Control Surfaces	
Hardness (ISO 7619)	75±5 shore A	
Abrasion Resistance (ISO 4649, method A)	≤200mm ³	
Indentation (EN433)	≤0,20mm	
Cigarette burning resistance (EN1399)	No burn	
Chemical resistance (EN423)	Resistant to chemical agents normally used for maintenance	
Dimensional Stability (EN424 - 6h/80°C)	≤0.4%	
Surface Resistance Top Layer (EN 100015.1-IEC61340)	About 10 ⁸ Ω	
Surface Resistance Bottom Layer (EN 100015.1-IEC61340)	About 10⁵Ω	

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the pioducts to which it relates. No licence of any intellectual poperty rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheets previously supplied check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.



http://www.farnell.com http://www.newark.com http://www.cpc.co.uk



ESD Monitored Workstation Kit Contents:

ESD Caution Sign

- Antistatic coating
- Self adhesive: 0.4mm thick PVC
- 300 x 150mm

Economy Wrist Strap Set

- A comfortable, fully adjustable wristband incorporating a 10mm press stud.
- Supplied complete with a durable coiled earth lead, with a 10-10mm press stud.

Straight Earth Lead

- Excellent quality for use with any kind of Field Service Kit or Table Mat
- Strong connection between the cord and 10mm stud
- Special conductive wire each containing 10 special conductive wires
- Outer covered with non-conductive PU
- Length: 12ft
- Diameter of cord: 2.4 mm
- Resistivity : 1M Ohm +/- 10%

Earth Bonding Point with 2x10mm Studs with Built In Tester

- Earth Bonding Point Boxes designed to be mounted on bench
- Black cord 3m long, can exit towards left or right
- 1 MΩ (1x10E6 ohms) 1/2 Watt resistor for each connector

Power Supply Unit for EBP

Earth Facility Bracket with M5 Binding Post

- · Serves as a grounding hub for earth bonding points, can receive several wires
- Supplied with mounting screws easy to mount
- Size: 40 x 45 x 12mm
- Supplied with instruction leaflet.

	Product Code:	Description:	Size:	Additional Notes:
	1762466	Monitored Workstation Kit	Mat 600 x 900mm	Blue (Ref: 069-0009)

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the poducts to which it relates. No licence of any intellectual poperty rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheets previously supplied check for themselves the Information and the suitability of the products for their purpose and not make any assume ton based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

