



"AMP", PART NO. & DATE CODE
 MARKED (WHITE) 1.58±0.38 [.062±.015] HIGH CHARS.
 IN AREA SHOWN WHEN HOUSING SIZE PERMITS





CAVITY IDENT. MARKED (WHITE)
 1.17±0.38 [.046±.015] HIGH CHARS. SECOND AND
 EVERY FIFTH CAVITY, ONE SIDE.





BASIC DIMENSION FOR
 ODD NUMBER OF SPACES (SEE THE TABLE)
 BASIC DIMENSION FOR
 EVEN NUMBER OF SPACES (SEE THE TABLE)

DETAIL Z



SECTION X-X



SECTION Y-Y
 ROTATED 90° CLOCKWISE

- 2 SEE TABLE FOR NUMBER OF DETENTS. DETENT ON THIS SIDE FOR HOUSINGS WITH ONE DETENT.
- 3 STRAIN RELIEF LOCATORS WILL APPEAR ON 20 POSITION AND LARGER HOUSINGS.
- 4 USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 5 THESE HOUSINGS ARE COMPATIBLE WITH ANY MOD II SHROUDED HEADER.
- 6 HOUSINGS WILL ACCOMMODATE ALL MOD IV, IV.5 AND MOD V CONTACTS.
- 7 MATERIAL: FLAME RETARDANT GLASS FILLED NYLON, COLOR: BLACK PER ASTM D4066.

MARKING	NO. OF DETENTS	D	NO. OF SPACES	NO. OF POSN	PART NUMBER
ALL	2	81.28 [3.200]	31	64	6-87631-6
NONE	2	81.28 [3.200]	31	64	6-87631-5
ALL	2	73.66 [2.900]	28	58	6-87631-4
NONE	2	73.66 [2.900]	28	58	6-87631-3
					6-87631-2
					6-87631-1
ALL	2	60.96 [2.400]	23	48	6-87631-0
NONE	2	60.96 [2.400]	23	48	5-87631-9
ALL	2	88.90 [3.500]	35	72	5-87631-8
NONE	2	88.90 [3.500]	35	72	5-87631-7
ALL	2	88.90 [3.500]	34	70	5-87631-6
NONE	2	88.90 [3.500]	34	70	5-87631-5
ALL	2	83.82 [3.300]	32	66	5-87631-4
NONE	2	83.82 [3.300]	32	66	5-87631-3
ALL	2	76.20 [3.000]	29	60	5-87631-2
NONE	2	76.20 [3.000]	29	60	5-87631-1
					5-87631-0
					4-87631-9
					4-87631-8
					4-87631-7
ALL	2	68.58 [2.700]	26	54	4-87631-6
NONE	2	68.58 [2.700]	26	54	4-87631-5
ALL	2	66.04 [2.600]	25	52	4-87631-4
NONE	2	66.04 [2.600]	25	52	4-87631-3
ALL	2	63.50 [2.500]	24	50	4-87631-2
NONE	2	63.50 [2.500]	24	50	4-87631-1
ALL	2	55.88 [2.200]	21	44	4-87631-0
NONE	2	55.88 [2.200]	21	44	3-87631-9
ALL	2	53.34 [2.100]	20	42	3-87631-8
NONE	2	53.34 [2.100]	20	42	3-87631-7
ALL	2	50.80 [2.000]	19	40	3-87631-6
NONE	2	50.80 [2.000]	19	40	3-87631-5
ALL	2	48.26 [1.900]	18	38	3-87631-4
NONE	2	48.26 [1.900]	18	38	3-87631-3
ALL	2	45.72 [1.800]	17	36	3-87631-2
NONE	2	45.72 [1.800]	17	36	3-87631-1
ALL	2	43.18 [1.700]	16	34	3-87631-0
NONE	2	43.18 [1.700]	16	34	2-87631-9
ALL	2	40.64 [1.600]	15	32	2-87631-8
NONE	2	40.64 [1.600]	15	32	2-87631-7
ALL	2	38.10 [1.500]	14	30	2-87631-6
NONE	2	38.10 [1.500]	14	30	2-87631-5
ALL	2	35.56 [1.400]	13	28	2-87631-4
NONE	2	35.56 [1.400]	13	28	2-87631-3
ALL	2	33.02 [1.300]	12	26	2-87631-2
NONE	2	33.02 [1.300]	12	26	2-87631-1
ALL	2	30.48 [1.200]	11	24	2-87631-0
NONE	2	30.48 [1.200]	11	24	1-87631-9
ALL	2	27.94 [1.100]	10	22	1-87631-8
NONE	2	27.94 [1.100]	10	22	1-87631-7
ALL	2	25.40 [1.000]	9	20	1-87631-6
NONE	2	25.40 [1.000]	9	20	1-87631-5
ALL	1	22.86 [.900]	8	18	1-87631-4
NONE	1	22.86 [.900]	8	18	1-87631-3
ALL	1	20.32 [.800]	7	16	1-87631-2
NONE	1	20.32 [.800]	7	16	1-87631-1
ALL	1	17.78 [.700]	6	14	1-87631-0
NONE	1	17.78 [.700]	6	14	87631-9
ALL	1	15.24 [.600]	5	12	87631-8
NONE	1	15.24 [.600]	5	12	87631-7
ALL	1	12.70 [.500]	4	10	87631-6
NONE	1	12.70 [.500]	4	10	87631-5
ALL	1	10.16 [.400]	3	8	87631-4
NONE	1	10.16 [.400]	3	8	87631-3
ALL	1	7.62 [.300]	2	6	87631-2
NONE	1	7.62 [.300]	2	6	87631-1

THIS DRAWING IS A CONTROLLED DOCUMENT. DIN E. BRANDBERG 09FEB94
 CHK: S. SHUEY 08NOV94
 APVD: D. DUPLER 08NOV94
 PRODUCT SPEC: ---
 APPLICATION SPEC: ---
 MATERIAL: --- FINISH: ---
 WEIGHT: ---
 CUSTOMER DRAWING

Tyco Electronics Corporation
 Harrisburg, PA 17105-3608

CONNECTOR, MOD IV,
 CRIMP SNAP-IN, WITH DETENT

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 87631
 SCALE: 4:1 SHEET 1 OF 1 REV: W1