

61729-0010BLF - USB : Type B, Receptacle, Through Hole, 30u GXT Contact, 4 Pins, Full Back Shield with Bright Tin Plating, 1.57 mm PCB, White HSG, Tube packing



www.fci.com

Specifications

General

Hold Down Style	Standard
Number of contacts	4
Orientation	Right Angle
Pin Orientation	Standard
Product Type	Receptacle
Shell Options	Back Shield
Style	B Type
Sensor Contact Options	without Sensor Contact
Series Number	61729
Single or Dual Stack	Single

Dimensional

Thickness (Board - recommended)	1.57 mm
Thickness (Panel - max)	2.67 mm

Mounting

Mounting flange / Hole options	None
Mounting style	Through Hole

Physical

Color (Housing)	White
Material (Housing)	Glass - Fiber Filled Thermoplastic, UL 94V-0
Plating (Contact area)	30u" GXT
Plating (Shell)	Pure Tin / Nickel Under Plating
Plating (Tail)	100u" Pure Tin

Approvals / Certifications

USB 2.0 Qualified	Yes
-------------------	-----

Other Features

Packaging (Options)	Tubes
---------------------	-------