



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.



Mounting Holes



REVISIONS		DOC. NO.	SPC-F005	Effective:	12/21/08	DCP No.	860
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
	A	RELEASED					
370	B	Redraw from indivd. dwgs	JWM	3/18/02	JC	3/27/02	JC

NOTES:

- Material: Black, Heat Stabilized Nylon
- Temperature Index: 105°C
- Flammability Rating: UL94V-2

SPC Type No.	Cross Section	Cable Size	Cable Type	Gauge (AWG)	Mounting Hole			Bushing		
					A (Diameter)	B (Flats)	C (Max. Panel Thickness)	D (Length)	E (Width)	
SRF-10	Flat	.120 x .220 [3.0 x 5.6]	SP-1 SPT-1	18/2 18/2	.437	.390	.062	.410	.484	
					[11.1]	[9.9]	[1.6]	[10.4]	[12.3]	
SRF-15	Flat	.120 x .300 [3.0 x 7.6]	SPT-1 SPT-2 HPN	18/3 18/2 18/2	.500	.465	.062	.406	.578	
					[12.7]	[11.8]	[1.6]	[10.3]	[14.7]	
SRF-30	Flat	.120 x .300 [3.0 x 7.6]	SPT-1 SPT-2 HPN	18/3 18/2 18/2	.500	.465	.100	.406	.578	
					[12.7]	[11.8]	[2.5]	[10.3]	[14.7]	
SRF-40	Flat	.160 x .410 [4.1 x 10.4]	SPT-2 HPN	16/3 16/3	.562	.530	.125	.609	.625	
					[14.3]	[13.5]	[3.2]	[15.5]	[15.9]	
SRF-50	Flat	.120 x .300 [3.0 x 7.6]	SPT-1	16/3	.506	.730	.125	.670	.750	
					[14.2]	[18.5]	[3.2]	[17.0]	[19.6]	

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SWE CONDITIONS OF USE ARE INTENDED FOR YOUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWING TITLE:
Strain Relief bushing

DRAWN BY: JC	DATE: 2/18/91	SIZE: A	DWG. NO.: TA-508	ELECTRONIC FILE: TA-508	REV: B
CHECKED BY:	DATE:				
APPROVED BY:	DATE:	SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1	DF 1