

Cordless Soldering Irons, 15 Watts

- Heats up to approx. 370°C in 6 seconds
- Fingertip control with safety-lock switch
- Longlife nickel cadmium batteries fully charged overnight
- Interchangeable tips
- Built-in work light
- Slim, lightweight balanced design
- WC110C packed in coloured carton consisting of soldering iron complete with tip WC 112 and battery charger
- WC100CPK packed in plastic case consisting of soldering iron complete with tip WC112, battery charger, 25 g solder, replacement tip WC111 and soldering aid tool



WC110C



WC100CPK



Type	Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
WC110C	0051604299	15	230	50	464	6
WC100CPK	0051605299	15	230	50	728	6

Tips for Cordless Soldering Irons

- For Soldering Irons WC110C and WC100CPK
- Tips with built-in heating element

Type	Code No.	Description	Width mm	Shelf Pack
WC111	0051611199	chisel	2,5	6
WC112	0051611099	chisel	1,5	6
WC113	0051611299	pointed	0,8	6

Butane Gas Operated Soldering Iron WP2 Pyropen Jr.

- Mini iron soldering and brazing that goes everywhere with temperature control
- Recharged in seconds
- This easy-to-handle butane gas operated soldering pen requires no power cord or batteries and is electrically completely neutral (no peaks)
- "Longlife" soldering tips deliver quick heat-up time
- Temperature control of soldering iron: 200-450°C
Hotblow feature: 430°C max., torch feature: 1300°C max.
All temperature are approximate
- Consist of WP2 Pyropen Jr., iron holder, cleaning sponge, tapered needle "Longlife" tip 0,5 mm (71-01-01) and gas-refill



Type	Code No.	Description	Weight g	Shelf Pack
WP2	0051606599	Pyropen Jr.	245	6