

## SMA, SMB, SMC Coaxial Cable Assemblies



- Quality turned brass connectors with PTFE insulators and silicon rubber gaskets
- Gold plated brass and passivated stainless steel bodies with gold plated contacts
- Manufactured to ensure compatibility with IEC mating face requirements and **US MIL-C-39029**

- Patchcord assemblies for wireless base station and general instrumentation applications

230395

Length (m)	Mftrs. List No.	Order Code	Price Each
<b>St Steel/Au RG316</b>			
<b>SMA 50Ω Plug to Plug</b>			
0.25	1337808-1	105-6167 ●	
0.5	1337808-2	105-6168 ●	
1	1337808-3	105-6169 ●	
<b>SMA 50Ω Plug to R/A Plug</b>			
0.25	1337810-1	105-6173 ●	
0.5	1337810-2	105-6174 ●	
1	1337810-3	105-6175 ●	
<b>SMA 50Ω R/A Plug to R/A Plug</b>			
0.25	1337812-1	105-6180 ●	
0.5	1337812-2	105-6182 ●	
1	1337812-3	105-6183 ●	
<b>Au/Au RG174</b>			
<b>SMA 50Ω Plug to Plug</b>			
0.25	1337809-1	105-6170 ●	
0.5	1337809-2	105-6171 ●	
1	1337809-3	105-6172 ●	
<b>SMA 50Ω Plug to R/A Plug</b>			
0.25	1337811-1	105-6176 ●	
0.5	1337811-2	105-6178 ●	
1	1337811-3	105-6179 ●	
<b>SMB 50Ω Plug to Plug</b>			
0.25	1337815-1	105-6187 ●	
<b>SMB 50Ω Plug to R/A Plug</b>			
0.5	1337815-2	105-6188 ●	
1	1337815-3	105-6191 ●	
<b>SMB 50Ω R/A Plug to R/A Plug</b>			
0.25	1337816-1	105-6192 ●	
0.5	1337816-2	105-6193 ●	
1	1337816-3	105-6194 ●	
<b>SMC 50Ω R/A Plug to R/A Plug</b>			
0.25	1337817-1	105-6195 ●	
0.5	1337817-2	105-6196 ●	
1	1337817-3	105-6197 ●	
<b>SMC 50Ω Plug to Plug</b>			
0.25	1337819-1	105-6202 ●	
0.5	1337819-2	105-6203 ●	
1	1337819-3	105-6204 ●	
<b>Au/Au RG316</b>			
<b>SMB 50Ω Plug to Plug</b>			
0.25	1337814-1	105-6184 ●	
0.5	1337814-2	105-6185 ●	
1	1337814-3	105-6186 ●	
<b>SMB 50Ω R/A Plug to R/A Plug</b>			
0.25	1337818-1	105-6198 ●	
2	1337818-4	105-6200 ●	
3	1337818-5	105-6201 ●	