

Datasheet

Product – SpeedyTie

Order Code – RTT750HR.NX900

Colour – Yellow, Red



Features & Benefits

The SpeedyTie® can be used many times because of its removable, patented trigger. Also this is a heavy duty releasable tie that can bear loads of up to 888N (200lbs). With a length of 750mm it suits a wide variety of applications and is easy to handle even when wearing work gloves. Any excess tail can be easily 'tucked away' in a second slot on the head. These ties are available in 'high visibility' yellow and in weatherproof black.

The versatility of the SpeedyTie® means that it is suitable for a multitude of applications. Originally developed for the 'offshore' industries, other uses include: construction, electrical installations, scaffolding sheet installations, exhibitions, trade fairs, and many more.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Yellow & Red
Operating Temp.	-40°C to +85°C Continuous (+105°C for 500 h)
Flammability	UL94 V2

Part No.	Product reference	Length (L)	Width (W)	Bundle Ø max.	Min Tensile Strength
RTT750HR.NX900	SpeedyTie	750	13	210	888

All dimensions in mm.