

Search: Select Location:

[Enclosures](#) | [Contract Manufacturing](#) | [Products](#) | [Company info](#) | [News & Events](#) | [Contacts](#) | [Downloads](#)

Product card: L 44 II



Sample photo

Product nbr: 4512299
 Description: Window for 36 modules
 Remarks: Smoked transparent cover
 Package: 22
 Unit: PCS
 Product group: ACCESSORIES
 EAN: 6418074035127
 SSTL number: 3421149
 Electric No. Denmark: 8212015416
 Electric No. Italy: 7590747
 Electric No. Sweden: 2540021

Dimensions:

Length (mm): 377
 Width (mm): 331
 Length (inch): 14.8
 Width (inch): 13.0

Materials:

Material: Polycarbonate

Temperatures:

Min temperature °C (short term): -40
 Max temperature °C (short term): 120
 Min temperature °C (continuous): -40
 Max temperature °C (continuous): 80
 Min temperature °F (short term): -40
 Max temperature °F (short term): 250
 Min temperature °F (continuous): -40
 Max temperature °F (continuous): 175

Rating:

Ingress Protection (EN 60529): IP 65

Product is connected to following catalogs:

Fibox catalogue : [GENERAL ACCESSORIES](#) : [INSPECTION WINDOWS](#)

[Enclosure search](#)

[Back to catalog](#)