Product card: L 12 II

Sample photo

Product nbr:

3730775

Support items:

Dimensional drawing (mm)

Description:

Window for 12

modules

Remarks:

Smoked transparent

cover

Package:

10

Unit:

PCS

Product group:

ACCESSORIES

EAN:

6418074036841

SSTL number:

3422652

Electric No. Italy:

7590740

Electric No. Sweden:

2539787

Dimensions:

Length (mm):

248

Width (mm):

128

Length (inch):

9.7

Width (inch):

5.0

Materials: Material:

Polycarbonate

Temperatures:

Min temperature °C (short term):

-40

120

Max temperature °C (short term): Min temperature °C (continuous):

-40

Max temperature °C (continuous):

80

Min temperature °F (short term): Max temperature °F (short term): -40

Min temperature °F (continuous):

250 -40

Max temperature °F (continuous):

175

Rating:

Ingress Protection (EN 60529):

IP 65

Product is connected to following catalogs:

Fibox catalogue : GENERAL ACCESSORIES : INSPECTION WINDOWS