



Sample photo

**Order symbol:** ABS 30/25-3  
**Product nbr:** 7585019

**EAN:** 6418074056795

**Description:** Enclosure, ABS  
**Remarks:** Smoked transparent cover

**Including:** Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

| Dimensions:             |                           |      |     | Rating:   |  |
|-------------------------|---------------------------|------|-----|---|--|
|                         | L                         | W    | H   |   |  |
| mm:                     | 296                       | 256  | 123 | <b>Ingress Protection (EN 60529):</b> IP 65       |  |
| inch:                   | 11.7                      | 10.1 | 4.8 | <b>Impact Resistance (EN 50102):</b> IK 07        |  |
| Materials:              |                           |      |     | <b>Electrical insulation:</b> Totally insulated   |  |
| <b>Material:</b>        | ABS                       |      |     | <b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes |  |
| <b>Base colour:</b>     | RAL 7035                  |      |     | <b>Flammability Rating (UL 746 C 5):</b> UL 94 HB |  |
| <b>Cover colour:</b>    | Smoked grey               |      |     | <b>Glow Wire Test (IEC 695-2-1) °C:</b> 650       |  |
| <b>Gasket material:</b> | EPDM and Polyurethane     |      |     | <b>NEMA Class:</b> NEMA 1, 3, 3R, 12, 13          |  |
| Temperatures:           |                           |      |     | Certificates:                                     |  |
| <b>Short term:</b>      | -40 ... 80 °C             |      |     | Gost R  |  |
| <b>Continuous:</b>      | -40 ... 60 °C             |      |     |   |  |
| <b>Short term:</b>      | -40 ... 175 °F            |      |     |   |  |
| <b>Continuous:</b>      | -40 ... 140 °F            |      |     |   |  |
| Accessories:            |                           |      |     |   |  |
| MP 30/25                | Mounting plate            |      |     |   |  |
| FP 30/25                | Front plate               |      |     |   |  |
| CM 30/25-3T             | Cover                     |      |     |   |  |
| SET 30/25-3             | Set of hinges and latches |      |     |   |  |

