



Order Code:	120-8854
Manufacturer Part No:	L08R5000Q1
LED Size:	5mm / T-1 3/4
LED Colour:	Orange
Typ Luminous Intensity:	4.3mcd
Viewing Angle:	68°
Forward Current:	30mA
Lens Shape:	Round
No. of Pins:	2
Current If Luminous Intensity:	10mA
External Length:	8.7mm
LED Colour Presentation:	Tinted diffused
Lead Length:	17.8mm
Lead Spacing:	2.54mm
Luminous Intensity:	4.3mcd
Max Current If:	30mA
Max PIV:	5V
Operating Temperature Range:	-25 °C to +85 °C
Typ Voltage Vf:	2.1V
Typ Wavelength:	635nm