

B STECKVERBINDER

CONNECTEURS

CONNECTORS

Für Renkverschluß A baionnette Twist lock		2polig mit Iso-Zapfen bzw. Ruhekont. 2 pôles, doigts Iso ou contact repos 2 pins, with insul. taps or n.c. contact	3polig DIN 41 524 3 pôles DIN 41 524 3 pins DIN 41 524	4polig Teilg. 72° 4 pôles pas 72° 4 pins 72° spacing	5polig Stereo DIN 41 524 5 pôles stéreo DIN 41 524 5 pins stereo DIN 41 524	5polig Teilg. 60° 5 pôles pas 60° 5 pins 60° spacing	6polig DIN 45 322 6 pôles DIN 45 322 6 pins DIN 45 322	7polig DIN 45 329 7 pôles DIN 45 329 7 pins DIN 45 329	8polig DIN 45 326 8 pôles DIN 45 326 8 pins DIN 45 326	
Kontaktanordnung Disposition des contacts Position of contacts										
Buchsen embases receptacles		Bestell-Nr. Article No. Part No.	71206-021	71206-031 * ¹⁾	71206-040 * ¹⁾	71206-051 * ¹⁾	71206-050 * ¹⁾	-	71206-070 * ¹⁾ 2)	71206-080 * ¹⁾ 2)
			¹⁾ Anschlußflähen auf ø 15,2 gespreizt cosses de raccordement, ø 15,2, en éventail solder terminals flared to a 15,2 mm DIAM		²⁾ Mit Flansch für Senkschrauben avec bride pour vis à tête conique with countersunk mounting flange					
Stecker fiches plugs	Stecker, gerade fiches – droites plugs – straight with twist-lock ring	Bestell-Nr. Article No. Part No.	71430-020	71430-030 *	71430-040 *	71430-050 *	71430-250 *	-	71430-070 *	71430-080 *
	Winkelstecker fiches coudée right angle plugs with twist-lock ring	Bestell-Nr. Article No. Part No.	-	71434-030 *	71434-040 *	71434-050 *	71434-250 *	-	-	-
Kupplung prolongateur coupling		Bestell-Nr. Article No. Part No.	71504-020	71506-030 *	71504-040 *	71506-050 *	71506-250 *	-	71506-071 *	71506-080 *