


機密等級:[]極機密[V]機密[]一般文件

| | | |
|-----------|------------|-------------|
| MOLD | INSIDE NO. | OUTSIDE NO. |
| DVI 29P M | 020580 | YD-199 |
| DVI 29P F | YD-198 | YD-198 |




注解

- 線 UL20276(30# 3C COAX)+(28#*1P+EAM)*4+28AWG*1P+28AWG*6C AEB
OD=8.5MM 外被顏色:米色3#
- 連接器 J1-DVI 24+5C MALE SOLDER MD TYPE W/TS
J2-DVI 24+5C FEMALE(RIVET NUT) MD TYPE
J1,J2-(PIN針鍍金) 內部加箔隔離
W/"" LOGO ON THE PIN1~8 SIDE
- 螺絲 4*33.0MM(#4-40 UNC) 顏色:米色3#
- 膠芯顏色:黑色 外模成型PVC顏色:米色3#
- 鐵粉芯(BRH15.5*28.5*10.5)
- 包裝 W/空白袋(右下角印"MADE IN CHINA")

| G.W. NO. | LENGTH |
|-----------------|----------|
| HCD167200000000 | 2M±0.05M |
| | |
| | |

| PIN OUT | | J1 | J2 |
|----------|----|------------|--------------------|
| (1P+S)-1 | 1 | RED | 1 |
| | 2 | WHITE | 2 |
| | 3 | DRAIN WIRE | 3 |
| | 9 | GREEN | 9 |
| (1P+S)-2 | 10 | WHITE | 10 |
| | 11 | DRAIN WIRE | 11 |
| (1P+S)-3 | 17 | BLUE | 17 |
| | 18 | WHITE | 18 |
| (1P+S)-4 | 19 | DRAIN WIRE | 19 |
| | 24 | BROWN | 24 |
| C1 | 23 | WHITE | 23 |
| | 22 | DRAIN WIRE | 22 |
| C2 | C1 | RED | C1 |
| | C2 | GREEN | C2 |
| C3 | C3 | BLUE | C3 |
| | C5 | BRAIDING | C5(RED+GREEN+BLUE) |
| PAIR | 6 | YELLOW | 6 |
| | 7 | ORANGE | 7 |
| C4 | 8 | BROWN | 8 |
| | 14 | VIOLET | C4 |
| SHELL | 15 | BLACK | 14 |
| | 16 | GREEN | 15 |
| | | RED | 16 |
| | | SHELL | SHELL |

本圖繪之產品符合RoHS
環境管理物質的要求



SCALE: 4:1

| 1-0 | AUG-16-2006 | 2214-060800006 |
|-------------------------------|---------------------------------------|------------------|
| REV | DESCRIPTION | ECN NO. |
| | | |
| DWG NAME: DVI 24+5C M/F CABLE | | |
| G, W, NO: | SEE THE TABLE | CUS. ID: |
| CUS NO: | | DWG. NO: DVI-126 |
| SHEET: 1/1 | TOLERANCE: . X _____ . XX _____ | UNIT: mm |
| | SCALE: 1:1 | DRAW. BY: |
| | | CHECKED |
| | | APPROVE |