

	PART NO.		REVISIONS							
	MCCQ-211A	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		-	А	RELEASED	Geetha	02/6/08	Suresh	02/6/08	G. C	17/6/08





## **Specifications:**

Rated current	: 20A.
Minimum insulation resistance	: 100MΩ at 500V dc.
Contact resistance	: $5m\Omega$ at 1A dc.
Minimum dielectric strength	: 1500V ac for 60 seconds.
Body material	: Nylon.
Supply standard wire-AWG/length	: 14 AWG/8 inches loop.
Interlock for multiple mounting.	
Contact	: Brass, tin/nickel plated.
To install fuses with "loop" type wires, simply	cut loop into two form separate wires of desired length.

## Part Number Table

Description	Part Number				
Fuseholder, In-Line, ATO, 20A	MCCQ-211A				

## http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Geetha	02/06/08	Automotive Fuse-Holders - ATO 20A In-Line				
		CHECKED BY:	DATE:	SIZE DWG NO.	M10001210	ELECTRONIC FILE	REV A	
		Suresh	02/06/08			1586597 DWG		
		APPROVED BY:	DATE:					
		G.Cook	17/06/08	SCALE: NTS	U.O.M.: mm	SHEET: 1 O	)F 1	