

DC740KA

129-3741

12 Volt 10 mm Cordless Drill Driver



Features

- Ergonomically designed trigger and rubber grip for comfort and ease of use
- Powerful 12 Volt drill driver for drilling and screwdriving applications
- Extremely compact and lightweight design for working in confined areas
- 10 mm single sleeve chuck and spindle lock for quick and easy bit change with one hand
- All metal gearing for efficient power transmission and longer tool life
- Modular design for easy access to key components and excellent serviceability
- Electric motor brake for added control
- Two speed settings, variable speed and reverse switch for maximum control
- 14 Position adjustable torque control for consistent screwdriving into a variety of materials with different screw sizes

Specifications	Voltage	12 V
Chuck Capacity		1.0-10 mm
Battery		NiCd 1.3 Ah
Power Output		190 Watts
No Load Speed		0-350 /0-1200 rpm
Max. Drilling Capacity [Wood]		25 mm
Max. Drilling Capacity [Metal]		10 mm
Weight		1.6 kg
Length		212 mm
Height		225 mm

Standard

- 1 hour charger
- 2 batteries
- Heavy duty carrying case