
Item no.: 231-535/001-000
Product description: HEADER; RIGHT ANGLE SOLDER PIN, 1 X 1 MM / 0.039 X 0.039 IN; 5 POLE; PIN SPACING 5.08 MM / 0.2 IN; MATING DIRECTION PARALLEL TO PCB; WITH CLOSED END



Packing unit 200 4*50 pieces

Pin spacing from	5,08 mm
Pin spacing from	0,2 in
pole count	5
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	12 A
Voltage CSA	300 V
Current CSA	10 A
Voltage UL	300 V
Current UL	10 A
Weight	1,77 g
Color	orange
Height	8,4 mm
Height	0,331 in
Width	28,6 mm
Width	1,126 in
Depth	12 mm
Depth	0,472 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
231-535/001-000	ABS	04-HG469925-PDA	400	12	0,8-2,5
231-535/001-000	BBJ	B/12/699/03	250	12	0,8-2,5
231-535/001-000	BV	11915/A0	400	16	2,5
231-535/001-000	CCA	DK2127	400	12	0,8-2,5
231-535/001-000	CSA	154112-1466354	300	10	1x1
231-535/001-000	CSM	017956	500/250	12	0,8-2,5
231-535/001-000	DEMKO	88126	250		2,5
231-535/001-000	GL	17296-00HH	400	12	0,8-2,5
231-535/001-000	KR	HMB05880-EL003	250/400	12/16	2,5
231-535/001-000	LR	96/20035	400	12	0,8-2,5
231-535/001-000	NEMKO	P94101840	250		2,5
231-535/001-000	RMR	11130002	400	12	0,8-2,5
231-535/001-000	RosTesT	B09523	400	12	0,8-2,5
231-535/001-000	UL	E45172	300	10	1x1
231-535/001-000	VDE	5675ÜGBI.2	250	12	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected