

Photo



Erem_Toolset_2400KMS.jpg

L x W x D: 270X170X50mm Weight:605g

2. Title	High Precision Swiss Tool Kit
-----------------	--------------------------------------

3. Series	▪ Erem 2400 MagicSense	ESD Tool Kit
------------------	-------------------------------	--------------

4. Description
<ul style="list-style-type: none"> • 3-piece tool kit in an ESD-safe plastic case • For use in electronics, PCB assembly, wire and connection handling • MagicSense moulded handle with soft touch for increased comfort and grip • Induction-hardened cutting edges in Rockwell hardness 64-65 HRC • High grade of hardness for exceptionally long life • High grade tool steel, non-reflecting surface, ESD-safe, resharpenable • Internal Erem Magic Spring: constant spring force, guarantees more than 1 million operations • High precision screw joint: smooth jaw action with no play, smooth cutting operation with no jaw overlapping • Maximum opening stop: the limited extent to which the handles can open prevent user hand fatigue

5. Model				
	Items			<i>Photo</i>
	2412E	Ergo, oval head, semi-flush	Most widely used head shape. It is robust and size for size offers the highest cutting capacity. Hard wire 0,5mm, medium hardness 1,0mm,Cu. 1,6mm	2412E.jpg
	2482E	Ergo, Tip cutter, 45° angled narrow head, flush	For precise cuts at different working angles. medium hardness 0,6mm,Cu. 1,2mm	2482E.jpg
	2411P	Ergo, Needel nose plier	With very precise, smooth and rounded jaws	2411P.jpg