

**Photo**

Erem\_Toolset\_3600KU.jpg

L x W x D: 255X220X55mm Weight:480g



<b>2. Title</b>	High Precision Swiss Tool Kit
-----------------	-------------------------------

<b>3. Series</b>	▪ Erem Toolset Universal	ESD Tool Kit
------------------	--------------------------	--------------

<b>4. Description</b>
<ul style="list-style-type: none"> <li>• 11- piece tool kit in an <b>ESD-safe</b> plastic case, 2 cutters, 1 plier, 2 tweezers, 6 screwdrivers</li> <li>• High-quality precision tweezers, cutters and screwdriver, non-reflecting surface, resharpenable</li> <li>• <b>Internal Erem Magic Spring:</b> constant spring force, guarantees more than 1 million operations</li> <li>• <b>High precision screw joint:</b> smooth jaw action with no play, smooth cutting operation with no jaw overlapping</li> <li>• <b>Maximum opening stop:</b> the limited extent to which the handles can open prevent user hand fatigue</li> <li>• For use in electronics assembly, the watchmaking industry, medicine</li> <li>• Precision screwdriver with hardened, durable Tips, for precision working in confined areas</li> </ul>

<b>5. Model</b>				
	<b>Items</b>			<i>Photo</i>
	XP600	Precision-screwdriver set for electronics	4 regular screwdrivers: 1,5x60mm/.059x2.36inch, 2,0 x 60mm/.078x2.36inch 2,5 x 60mm/098x2.36inch 3,0 x 60mm/.118x2.36inch - Philips Nr. 0 - Philips Nr. 00	
	2412E	Ergo, oval head, semi-flush	Most widely used head shape. It is robust and size for size offers the highest cutting capacity. Hard wire 0,5mm, medium hardness 1,0mm,Cu. 1,6mm	2412E.jpg

	2442P	Ergo, flat nose plier	With smooth jaws, precision-machined edges, e.g. for gripping flat workpieces	2442P.jpg
	622NB	Tip cutter, flush, relieved, long, fine head	Miniatur cutter for excellent access, medium hardness 0,6mmCu. 0,8 mm	622NB.jpg
	AASA	Precision tweezers	Pointed Tipps straight, spezial stainless steel, non-magnetic	AASA.jpg
	2ASASL	Precision tweezers	With flat rounded tips, Tip widths 2mm/.078inch, spezial stainless steel, non-magnetic	2ASASL.jpg