

# PT-200 PRO-TORCH™

## Butane Powered Child Resistant Automatic Ignition System

### SPECIFICATIONS:

PT-200 PRO-TORCH™	
Dimensions	H-139 mm(5.5inch) L-101 mm(4.0inch) Grip Dia-34 mm(1.35inch) Base-61 mm(2.4inch)
Weight (w / o fuel)	145 g (empty)
Fuel	Butane
Hours of nonstop Burning	60 Minutes (min. setting)
Flame Temperature	1300°C (blue flame)

### Features:

State of the art Waterproof Piezo Electronic Ignition system. Up to 90 minutes use on each filling. Powerful Wind-Resistant flame. Compact size with ergonomic grip. Child-resistant ignition for safety. Easily refilled with any brand of butane gas. Flame adjustment for any size job.

### Instructions:

- Prior to initial use, fill torch with butane fuel as described below
- To fill gas tank, turn unit upside down and firmly push the butane can nozzle into the filling valve (fig. **D**).  
The tank should be filled in approximately ten seconds.  
Please allow a few minutes after filling for the gas to stabilize.
- To ignite the torch:
  - Slide the Gas Regulator Lever to the "on" position (fig. **A**).
  - Rotate the igniter button slightly to the left (counterclockwise) to release the childproof lock (fig. **B**) and then push in to ignite (fig. **C**).
  - The flame can then be adjusted by sliding the Regulator Lever.
- To shut off the torch, simply move the Regulator Lever to the far left and until you feel or hear it click into the lock-off position.

### Warnings:

- Do not touch flame guard while in use or until sufficient time has passed for cooling.
- Do not immerse heated parts or items in water, allow to cool naturally.
- Use only butane gas in the torch. Do not use propane gas or any other types of fluids.
- Do not store in a temperature exceeding 40°C / 104°F.
- Keep away from eyes at all times.
- Keep this unit out of the reach of children.
- The flame of the torch is nearly invisible in bright light or sunlight.
- Make sure that gas flow is turned off when not in use.

