

tesa worldwide | Extranet login | Sitemap | Search | Contact | www.tesa.com |

# INDUSTRIES | OFFICE & AT HOME | ADHESIVE TAPE RANGE | COMPANY | HINTS & TIPS |

- \_ Automotive
- \_ Automotive Refinishing
- \_ Corrugated Cardboard Industry
- \_ Craftsmen and Trades
- \_ Fairs & Exhibitions
- \_ Flexographic Printing
- \_ Furniture Industry
- \_ Marine Industry
- \_ Paper & Print
- \_ Packaging & Logistics
- \_ Painting and Decorating
- \_ Trims & Profile Producers
- \_ Security, Brand Protection & Identification
- \_ Solar Industry
- \_ Health Markets
- \_ Product Range
- \_ tesanet Distributors

# < back to search results

PRODUCT INFORMATION

# tesa® 4330

High performance paper masking tape for painting with oven drying up to 140  $^{\circ}\text{C}$ 

# **Product Description**

tesa® 4330 is a finely crêped, flexible, wet resistant masking tape with a high tensile

#### Main Applications

Further applications are e.g.

- masking of circuit boards before platingcable bundling
- packaging

#### Technical Data

Backing material	slightly-creped paper
Type of adhesive	natural rubber
Total thickness	175 µm
Adhesion to steel	4.8 N/cm
Elongation at break	12 %
Tensile strength	42 N/cm
Temperature resistance	140 °C

#### Properties

Easy to remove	yes
Paint anchorage	++
Sharp colour Edge	+
Conformability	+
Hand tearability	++

Evaluation across relevant tesa assortment: ++ very good, + good, o medium, - low

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you

# back to top ↑

Print view | Bookmark

© tesa UK Ltd. - A tesa Company | Imprint | Legal Terms | Privacy Policy |



# Contact details:

General: + 44 (0)1908 211333 C/S Dept: + 44 (0)1908 500333

Contact us

Adhesive Tape Descriptions

# Adhesive Tape Guide

Know your adhesive tapes, from Double Sided Tape, Cloth Tape, Safety Tape, Masking Tape to Splicing Tape, Packaging Tape, Strapping Tape