

**ebm-papst Landshut GmbH**

Hofmark-Aich-Straße 25

84030 Landshut

Phone: +49 871 707-0

Fax: +49 871 707-465

www.ebmpapst.cominfo3@de.ebmpapst.com**Nominal data**


Type	QLK45/1800-2518L	
Nominal voltage	[VAC]	230
Frequency	[Hz]	50
Speed	[min ⁻¹]	2350
Power input	[W]	26
Current draw	[A]	,245
Max. back pressure	[Pa]	67
Min. ambient temperature	[°C]	0
Max. ambient temperature	[°C]	60
Air flow	[m ³ /h]	125

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Technical features

Dimensions	45 mm
Connection line	Flat plug 3.6 x 0.8
Line	Compact series
Mounting position	Horizontal or vertical with motor below
Insulation class	"B" F or H also available on request
Mass	0.85 kg


Product drawing



AC tangential blower

forward curved

Charts: Air flow



AC tangential blower

forward curved

Charts: Speed

