

		REVISIONS																	
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE																	
										<p>RECOMMENDED CABLE STRIPPING DIM'S</p>									
					<p>NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)</p> <p>1. BRASS PER QQ-B-626 2. BRASS PER QQ-B-613 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE 4. NICKEL PL. 200 MIN. THICK OVER COPPER STRIKE 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE 6. JIS H 3250, C 2700</p>					<p>1. CRIMPED FERRULE HEX CRIMP SIZE .213" 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"</p>									
9	FERRULE	NOTE 6	NOTE 3	1	FR-635/56X127	DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				PART NO. B1121A1-ND3G-1A-50		<h1 style="text-align: center;">Amphenol</h1>							
8	CONTACT PIN	NOTE 1	NOTE 5	1	B50000-8-25/1					APPROVED DATE 10-11-01'									
7	WASHER	NOTE 2	NOTE 3	1	WS-128/9X08	CHECKED DATE 10-11-01'		TITLE BNC CRIMP PLUG											
6	SPRING	SK5	NOTE 4	1	B50000-6	DRAWN DATE 10-11-01'						DRAWING NO. KJ-B1121A1-ND3G-223U-50							
5	RETAINER RING	NOTE 1	NOTE 3	1	B50000-5	FILE NO.		ITEM NO.											
4	GASKET	RUBBER	RED	1	GS-115/8X15														
3	INSULATOR	DELTRIN	NATURAL	1	B50000-3-50-A														
2	BODY	NOTE 1	NOTE 3	1	B50000-2-427/31														
1	SHELL	NOTE 1	NOTE 3	1	B50000-1-B														
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	A	FILE NO.									