



1	2	3	4	5	6	7	8
ISS	ZONE	REVISIONS					
		DESCRIPTION\PER REQUEST\DATE					



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
2. BRASS PER QQ-B-613
3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
4. NICKEL PL. 200 MIN. THICK OVER COPPER STRIKE
5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK
6. PTFE MIL-P-19468
7. JIS H 3250, C 3501

11	NUT	NOTE 1	NOTE 3	1	B5291-14
10	FERRULE	NOTE 7	NOTE 3	1	FR-52/44-38/3 X14
9	WASHER	NOTE 2	NOTE 3	1	WS-128/9X08
8	SPRING	SK5	NOTE 4	2	B50000-6
7	RETAINER RING	NOTE 1	NOTE 3	1	B50000-5
6	GASKET	RUBBER	RED	1	GS-115/8X15
5	CONTACT PIN	NOTE 1	NOTE 5	1	B5091-6-50
4	INSULATOR	NOTE 6	NATURAL	1	ATC B-3000-3T -50
3	BARREL	NOTE 1	NOTE 3	1	B5091-3-38/17
2	HOUSING	NOTE 1	NOTE 3	1	B5091-2
1	SHELL	NOTE 1	NOTE 3	1	B50000-1-B
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

PART NO. B1112E1-NT3G-5-50

Amphenol

TITLE BNC R/A CRIMP PLUG
(FOR RG-174/U,188A/U,316/U)

DRAWING NO. KU-B1112E1-NT3G-316U-50

ITEM NO.

1

2

3

4

5

6

7

8