


ISS	ZONE	DESCRIPTION \ PER REQUEST \ DATE



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
 1. BRASS PER QQ-B-626
 2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 3. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 4. PTFE MIL-P-19468

NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.
7	RETAINER RING	SUS 304	NATURAL	2	NS000-7-C
6	GASKET	SILICONE	RED	2	GS-156/8X15
5	CONTACT PIN	NOTE 1	NOTE 3	1	NS900-5-B
4	INSULATOR	NOTE 4	NATURAL	1	NS900-4T-50-A
3	CONTACT BODY	NOTE 1	NOTE 2	2	NS000-5
2	BODY	NOTE 1	NOTE 2	1	NS900-2
1	SHELL	NOTE 1	NOTE 2	2	NS000-1-B

DIMENSIONS ARE IN MILLIMETERS	
UNLESS OTHERWISE SPECIFIED	TOLERANCES
0.5-6	= ±0.2
6-50	= ±0.4
30-120	= ±0.6
120-315	= ±1
315-1000	= ±1.6
1000-2000	= ±2.4

PART NO.	N2071A1-NT3G-50
APPROVED	DATE
CHECKED	DATE
DRAWN	DATE

TITLE	N MALE TO MALE ADAPTOR
DRAWING NO.	KJ-N2071A1-NT3G-50
ITBM NO.	

1 2 3 4 5 6 7 8