

MATERIALS AND FINISHES

PART NO. 89761-1760/89761-1761
89761-1762/89761-1763

SSMCX PLUG(73415-4680)
BODY, BRASS
PLATED GOLD

CENTER CONTACT, BRASS
PLATED GOLD

OUTER CONTACT, BeCu
PLATED GOLD

INSULATOR, PTFE

HEAT SHRINK TUBE, VERSAFIT V2
COLOR BLACK

CABLE 132


PACKAGING BY POLYBAG

PART NO. 89761-1764

SSMCX PLUG(73415-4684)
BODY, BERYLLIUM COPPER
PLATED TRI-METAL

CENTER CONTACT, BERYLLIUM COPPER
PLATED GOLD OVER TRI-METAL

OUTER CONTACT, BERYLLIUM COPPER
PLATED GOLD OVER TRI-METAL



MINIMUM LENGTH

PS-73598-0220 SSMCX SPECIFICATION
SPECIFICATION DESCRIPTION

89761-1764	5.906±.197	150.00±5.00	NON MAGNETIC
89761-1763	3.500±.197	88.90±5.00	GENERAL TYPE
89761-1762	3.937±.197	100.00±5.00	GENERAL TYPE
89761-1761	4.921±.197	125.00±5.00	GENERAL TYPE
89761-1760	5.906±.197	150.00±5.00	GENERAL TYPE
PART NO.	N	MM	DESCRIPTION
DIM	A		

CHG: ADDED P/N 89761/1764 EC NO: URF2007-0239 DRWN: MCHANDS CHKD: APPR: HUANG	2006/12/19 2006/12/28 2006/12/28
--	--

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)
▲-0	4 PLACES ± .000
▼-0	3 PLACES ± .000
▽-0	2 PLACES ± .000
△-0	1 PLATE ± .000
	ANGULAR ± 2°

DESIGNED BY JOHN	DATE 2006/04/07
CHECKED BY KERRIE	DATE 2006/04/07
APPROVED BY MISEN	DATE 2006/04/07

SCALE DIMENSION UNITS METRIC	TITLE SSMCX PLUG TO SSMCX PLUG WITH 132 CABLE CA-SSMCX/SSMCX
THIRD ANGLE PROJECTION	MOLEX INCORPORATED
	SD-89761-176
	SHEET NO. 1 OF 1