

**Rated Voltage : 12V DC**

**Starting Voltage : 8V**

**Operating Voltage : 12V**

**Rated Current : 0.07A**

**Power consumption : 0.84W**

**Speed : 5000rpm**

**Air Flow : 4.93 cfm**

**Static Pressure : 3.61 mm-H<sub>2</sub>O**

**Noise : <21dba**